

# nVent CADDY Speed Link SLK with Loop



## FEATURES

Complete system includes wire, locking device and pre-assembled loop end fitting

Easy and flexible solution attaches to building structures

Wire rope wraps around structure and through loop for quick installation

Ideal for attaching to purlins, beams and other structural members

Works well in tight or confined spaces

Loop attaches directly to pipe, ductwork or other hanging assemblies

**Material:** Steel; Polypropylene; Zinc Alloy  
**Finish:** Electrogalvanized  
**Static Load Safety Factor:** 5:1  
**Complies With:** SMACNA HVAC-DCS



## SPECIFICATIONS

Table 1/2



| Catalog Number | Article Number | Wire Rope Diameter | Wire Rope Length | Length (L) | Height (H) | Width (W) |
|----------------|----------------|--------------------|------------------|------------|------------|-----------|
| SLK15L1LP      | 196601         | 1.5 mm             | 1m               | 101.6mm    | 55 mm      | 19 mm     |
| SLK15L1LPR2    | 196628         | 1.5 mm             | 1m               | 101.6mm    | 55 mm      | 19 mm     |
| SLK15L2LP      | 196514         | 1.5 mm             | 2m               | 101.6mm    | 55 mm      | 19 mm     |
| SLK15L2LPR2    | 196629         | 1.5 mm             | 2m               | 101.6mm    | 55 mm      | 19 mm     |
| SLK15L3LP      | 196515         | 1.5 mm             | 3m               | 101.6mm    | 55 mm      | 19 mm     |
| SLK15L3LPR2    | 196630         | 1.5 mm             | 3m               | 101.6mm    | 55 mm      | 19 mm     |
| SLK15L5LP      | 196516         | 1.5 mm             | 5m               | 101.6mm    | 55 mm      | 19 mm     |
| SLK2L10LP      | 196606         | 2 mm               | 10m              | 101.6mm    | 55 mm      | 19 mm     |
| SLK2L1LP       | 196604         | 2 mm               | 1m               | 101.6mm    | 55 mm      | 19 mm     |
| SLK2L2LP       | 196543         | 2 mm               | 2m               | 101.6mm    | 55 mm      | 19 mm     |
| SLK2L3LP       | 196544         | 2 mm               | 3m               | 101.6mm    | 55 mm      | 19 mm     |


| Catalog Number | Article Number | Wire Rope Diameter | Wire Rope Length | Length (L) | Height (H) | Width (W) |
|----------------|----------------|--------------------|------------------|------------|------------|-----------|
| SLK2L5LP       | 196545         | 2 mm               | 5m               | 101.6mm    | 55 mm      | 19 mm     |
| SLK3L10LP      | 196711         | 3 mm               | 10m              | 101.6mm    | 62 mm      | 24 mm     |
| SLK3L2LP       | 196707         | 3 mm               | 2m               | 101.6mm    | 62 mm      | 24 mm     |
| SLK3L3LP       | 196708         | 3 mm               | 3m               | 101.6mm    | 62 mm      | 24 mm     |
| SLK3L5LP       | 196709         | 3 mm               | 5m               | 101.6mm    | 62 mm      | 24 mm     |

Table 2/2

| Catalog Number | Article Number | Thickness (T) | Angle (a) | Static Load | Certifications  |
|----------------|----------------|---------------|-----------|-------------|-----------------|
| SLK15L1LP      | 196601         | 12.5 mm       | 90 ° Max  | 195N        | cUL, SMACNA, UL |
| SLK15L1LPR2    | 196628         | 12.5 mm       | 90 ° Max  | 195N        | UL, SMACNA, cUL |
| SLK15L2LP      | 196514         | 12.5 mm       | 90 ° Max  | 195N        | SMACNA, cUL, UL |
| SLK15L2LPR2    | 196629         | 12.5 mm       | 90 ° Max  | 195N        | cUL, UL, SMACNA |
| SLK15L3LP      | 196515         | 12.5 mm       | 90 ° Max  | 195N        | UL, cUL, SMACNA |
| SLK15L3LPR2    | 196630         | 12.5 mm       | 90 ° Max  | 195N        | cUL, UL, SMACNA |
| SLK15L5LP      | 196516         | 12.5 mm       | 90 ° Max  | 195N        | cUL, SMACNA, UL |
| SLK2L10LP      | 196606         | 12.5 mm       | 90 ° Max  | 440N        | SMACNA, UL, cUL |
| SLK2L1LP       | 196604         | 12.5 mm       | 90 ° Max  | 440N        | SMACNA, UL, cUL |
| SLK2L2LP       | 196543         | 12.5 mm       | 90 ° Max  | 440N        | UL, SMACNA, cUL |
| SLK2L3LP       | 196544         | 12.5 mm       | 90 ° Max  | 440N        | SMACNA, cUL, UL |
| SLK2L5LP       | 196545         | 12.5 mm       | 90 ° Max  | 440N        | UL, SMACNA, cUL |
| SLK3L10LP      | 196711         | 16 mm         | 90 ° Max  | 890N        | SMACNA          |
| SLK3L2LP       | 196707         | 16 mm         | 90 ° Max  | 890N        | SMACNA          |
| SLK3L3LP       | 196708         | 16 mm         | 90 ° Max  | 890N        | SMACNA          |
| SLK3L5LP       | 196709         | 16 mm         | 90 ° Max  | 890N        | SMACNA          |

## DIAGRAMS





## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

### Europe

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

### Europe

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

### APAC

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

