

TDS Replacement Module



FEATURES

Replacement module for TDS Din Rail Series and TDX Modular Series

Max Discharge Current (Imax): 50kA 8/20 μ s



SPECIFICATIONS

Table 1/1


Catalog Number	TDS150M150	TDS150M240	TDS150M277	TDS150M440	TDS150M560
Nominal System Voltage (Un)	120 - 150 VAC	220 - 240 VAC	240 - 277 VAC	420 - 440 VAC	480 - 560 VAC
Max Continuous Operating Voltage (Uc)	170 VAC	275 VAC	320 VAC	480 VAC	610 VAC
Voltage Protection Rating (VPR)	600 V @ 3 kA 1000 V @ 20 kA	900 V @ 3 kA 1200 V @ 20 kA	1000 V @ 3 kA 1600 V @ 20 kA	1500 V @ 3 kA 2200 V @ 20 kA	1800 V @ 3 kA 2400 V @ 20 kA
Nominal Discharge Current (In)	20kA 8/20 μ s	20kA 8/20 μ s	20kA 8/20 μ s	20kA 8/20 μ s	20kA 8/20 μ s
Frequency	0 - 100 Hz	0 - 100 Hz	0 - 100 Hz	0 - 100 Hz	0 - 100 Hz
Enclosure Material	UL® 94V-0 Thermoplastic	UL® 94V-0 Thermoplastic	UL® 94V-0 Thermoplastic	UL® 94V-0 Thermoplastic	UL® 94V-0 Thermoplastic
Temperature	-40 to 80 °C	-40 to 80 °C	-40 to 80 °C	-40 to 80 °C	-40 to 80 °C
Module Width	1 M	1 M	1 M	1 M	1 M

Catalog Number	TDS150M150	TDS150M240	TDS150M277	TDS150M440	TDS150M560
Depth (D)	48mm	49mm	49mm	49mm	49mm
Height (H)	45 mm	45 mm	45 mm	45 mm	45 mm
Width (W)	18 mm	18 mm	18 mm	18 mm	18 mm
Unit Weight	0.07 kg	0.07 kg	0.07 kg	0.07 kg	0.07 kg

ADDITIONAL PRODUCT DETAILS

Remove black pin when using with TDX modular units.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.