

E-Series Indoor Cooling Unit



The nVent HOFFMAN E-Series range is specially designed and developed to meet the essential requirements of Industrial customers in India. Easy to specify, ready to use and simple to install, the E-series is available in four sizes: 500W, 1000W, 1500W and 2000W. All units are rated IP54, and have an operating temperature range from 20 C to 50 C.

FEATURES

Description: Units in the E-Series have a wide operating temperature range from 10 C to 50 C. Standard models come with powder-coated sheet metal, as well as a digital temperature controller with an LED display, and a built-in alarm and door switch interlock.

Finish: Powder-coated sheet metal structure

Protection: IP54

Temperature limits inside: 25 C° to 50 C°

Temperature limits outside: 20 C° to 50 C°

Type of connection: Terminal block

SPECIFICATIONS

Catalog Number	Height	Width	Depth	Nominal Voltage	Nominal Capacity Watts	Material
E060502M01	600mm	279mm	230mm	230V	500W	Mild Steel
E101002M01	950mm	400mm	260mm	230V	1000W	Mild Steel
E101502M01	950mm	400mm	260mm	230V	1500W	Mild Steel
E102002M01	950mm	400mm	305mm	230V	2000W	Mild Steel

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.