



		$\Delta T_{\text{air}} = 40^\circ\text{C}$ can be simplified: $\Delta T_{\text{air}} = 50^\circ\text{C}$ simplification not recommended			
height h normal $\times 2$		-	+	+	normal $\times 2$ required
		+	normal $\times 2$ for thermal insulation	normal $\times 2$ for thermal insulation and normal $\times 2$ for thermal insulation	
height h thermal $\times 2$		normal $\times 2$ for height	normal $\times 2$ for thermal insulation	-	
		+	+	-	-
thermal $\times 2$ side panel					
		light $\times 1$	flashes $\times 2$	slings $\times 2$	padding $\times 2$

34566-742

FEATURES

Aluminum extrusion, anodized finish, conductive contact surface



Gross Weight: 0.102kg

nVent.com/SCHROFF | 1

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff

