

# nVent CADDY Speed Link Catenary Kit, 20 m Length

## CATALOG NUMBER

**SLK6L20**

## FEATURES

Kit includes precut length of fuse-cut cable to avoid fraying, pre-assembled hook end fitting and tool-free locking device to save installation time

Fastens to the building structure by looping around and hooking to wire rope

Hook end-fitting easily attaches to eye nut

Spring latch helps provide secure connection



## PRODUCT ATTRIBUTES

Article Number: 196803

Material: Steel;Zinc Alloy;Polypropylene

Finish: Electrogalvanized;Hot-Dip Galvanized

Wire Rope Diameter: 6 mm

Wire Rope Length: 20m

A: 75 mm

B: 40 mm

C: 15 mm

Height (H): 108 mm

Width (W): 41 mm

Thickness (T): 30 mm

Angle (a): 60 ° Max

## ADDITIONAL PRODUCT DETAILS

Wire Rope Length is measured from the end of the wire rope to the hook side of the swage.

Static load 1 represents a point load in the center of the catenary installation. Static load 2 represents a two or three point distributed load on the catenary installation. Static load 3 represents a four or more point distributed load on the catenary installation.

Preload of the wire rope must be applied using Catenary Tensioning Tool.

| Horizontal Intallation |        |        |
|------------------------|--------|--------|
| Preload                | 1000 N | 450 N  |
| Static Load 1 (F1)     | 490 N  | 590 N  |
| Static Load 2 (F2)     | 880 N  | 1080 N |
| Static Load 3 (F3)     | 980 N  | 1180 N |
| Vertical Installation  |        |        |
| Static Load 4 (F4)     | 4440 N |        |

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

#### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

#### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

#### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

#### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

