

# HD Heavy Duty Pipe Clamp



## FEATURES

Fillet welded connector nut has flats to accommodate spanners

Easy open flange for pipe sizes less than 4"

Category II noise reduction according to DIN EN ISO 3822-1

Compliant for sound insulation design according to DIN 4109

Reaction-to-fire classification is "E" in compliance with DIN EN 13501-1

**Material:** Steel;EPDM-SBR Rubber  
**Finish:** Electrogalvanized  
**Temperature:** -50 to 110 °C  
**Color:** Black



## SPECIFICATIONS

Table 1/2

| Catalog Number | Article Number | Outer Diameter (OD) | NB/DN | Rod Size (RS) | Width (W) | Thickness (T) |
|----------------|----------------|---------------------|-------|---------------|-----------|---------------|
| HDI023         | 577034         | 19 - 23 mm          | 15    | M8, M10       | 30 mm     | 2.5 mm        |
| HDI028         | 577035         | 24 - 28 mm          | 20    | M8, M10       | 30 mm     | 2.5 mm        |
| HDI045         | 577038         | 40 - 45 mm          | 32    | M8, M10       | 30 mm     | 2.5 mm        |
| HDI058         | 577040         | 53 - 58 mm          |       | M8, M10       | 30 mm     | 2.5 mm        |
| HDI065         | 577041         | 60 - 65 mm          | 50    | M8, M10       | 30 mm     | 2.5 mm        |
| HDI078         | 577043         | 73 - 78 mm          | 65    | M10, M12      | 30 mm     | 3 mm          |
| HDI116         | 577048         | 108 - 116 mm        | 100   | M10, M12      | 30 mm     | 3 mm          |
| HDI145         | 577052         | 138 - 145 mm        | 125   | M12, M16      | 40 mm     | 4 mm          |
| HDI273         | 577066         | 265 - 273 mm        | 250   | M16, M20      | 40 mm     | 4 mm          |


Table 2/2

| Catalog Number | Article Number | Screw Diameter (Sc) | Screw Diameter metric (Sc) | Screw Length (L) | Static Load |
|----------------|----------------|---------------------|----------------------------|------------------|-------------|
| HDI023         | 577034         | 6 mm                | M6                         | 30mm             | 2000N       |
| HDI028         | 577035         | 6 mm                | M6                         | 30mm             | 2000N       |
| HDI045         | 577038         | 6 mm                | M6                         | 30mm             | 2000N       |
| HDI058         | 577040         | 6 mm                | M6                         | 30mm             | 2000N       |
| HDI065         | 577041         | 8 mm                | M8                         | 40mm             | 2000N       |
| HDI078         | 577043         | 8 mm                | M8                         | 40mm             | 3500N       |
| HDI116         | 577048         | 8 mm                | M8                         | 40mm             | 3500N       |
| HDI145         | 577052         | 10 mm               | M10                        | 40mm             | 5000N       |
| HDI273         | 577066         | 12 mm               | M12                        | 40mm             | 10000N      |

## ADDITIONAL PRODUCT DETAILS

Lining is EPDM rubber.

## DIAGRAMS



## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

#### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

#### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

#### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

#### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

