

HFF Steel Nailing Plate



The HFF nailing plate is sold separately from the A12 couplers. The plates easily attach to the couplers by orienting the hexagon opening in the plate to the coupler and then rotating the plate 15 degrees.

Used in segmental pour and closure pour applications. Permanent form saving plates allow easy attachment to form work, eliminating costly damage to the forms.

FEATURES

Designed for use with the A12 coupler families

Positively locks onto the hexagon-shaped coupler

Easy to install

No special tools required

Material: Spring Steel

SPECIFICATIONS

Table 1/2

Catalog Number	Article Number	Rebar Size, Metric	Rebar Size, US	Rebar Size, Canada	Length (L)	Hex Width (W)
EL1820HFF	152860	18 mm, 20 mm	#6	20M	50mm	27 mm
EL2225HFF	154420	22 mm, 25 mm	#7, #8	25M	70mm	36 mm
EL1012HFF	152840	10 mm, 12 mm	#3, #4	10M	50mm	17 mm
EL1416HFF	152850	14 mm, 16 mm	#5	15M	50mm	22 mm

Table 2/2


Catalog Number	Article Number	Height (H)	Package Quantity
EL1820HFF	152860	5 mm	100
EL2225HFF	154420	5 mm	75
EL1012HFF	152840	5 mm	100
EL1416HFF	152850	5 mm	100

ADDITIONAL PRODUCT DETAILS

Can also be used on A2N couplers.

Always wear gloves when installing plates to couplers.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE