



		Δ° can be simplified		Δ° combination not recommended	
100% Δ° $\rightarrow$ 100% Δ°	Aluminum Δ° $\rightarrow$ 100% Δ°		-	+	+
	Aluminum Δ° $\rightarrow$ 100% Δ°		+	aluminum Δ° flange (no connection)	aluminum Δ° flange and aluminum Δ° flange
100% Δ° $\rightarrow$ 100% Δ°	Aluminum Δ° $\rightarrow$ 100% Δ°		aluminum Δ° flange	aluminum Δ° flange	-
	Aluminum Δ° $\rightarrow$ 100% Δ°		+	-	-
100% Δ° $\rightarrow$ 100% Δ°	Aluminum Δ° $\rightarrow$ 100% Δ°		light Δ° 1	flange Δ° 2	flange Δ° 3
	Aluminum Δ° $\rightarrow$ 100% Δ°		flange Δ° 4	flange Δ° 5	flange Δ° 6

34566-720

FEATURES

Aluminum extrusion, anodized finish, conductive contact surface



Net Weight: 0.056kg

nVent.com/SCHROFF | 1

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff

