


Signal Reference Grid



FEATURES

Provides a low impedance equipotential plane to protect sensitive electronic equipment from transient noise

Pre-engineered welded grid of 26 gauge copper strips reduces voltage differences between interconnected electronic equipment

Welded connections do not deteriorate, corrode or loosen with time

Can be easily field-welded to suit any size computer room

Complies with IEEE® Standard 1100-1992

Material: Copper




SPECIFICATIONS

Catalog Number	Article Number	Length 1 (L1)	Width 1 (W1)	Grid Spacing (L2 x W2)	Thickness (T)	Strip Width
SRGBD100	167901	30500 mm	3.05 m	609.6 mm x 609.6 mm	0.4 mm	50.4mm
SRGBE100	167902	30480 mm	3.66 m	609.6 mm x 609.6 mm	0.4 mm	50.4mm

ADDITIONAL PRODUCT DETAILS

Custom sizes available upon request. Contact your nVent ERICO representative for more information.



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America	Europe	Europe	APAC
+1.800.753.9221	Netherlands:	Germany:	Shanghai:
Option 1 – Customer Care	+31 800-0200135	800 1890272	+ 86 21 2412 1618/19
Option 2 – Technical	France:	Other Countries:	Sydney:
Support	+33 800 901 793	+31 13 5835404	+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE