

nVent CADDY Pyramid H-Frame Kit



FEATURES

- Foam or rubber bottom offers low abrasion interface for better roof membrane protection
- Compatible with roof surfaces including single ply, bituminous, metal and spray foam
- Provides superior load distribution, even with varying rooftop surfaces
- Rubber rooftop interface ideal for solar panel array installations
- Kit includes 2 post bases with pre-installed mounting hardware, 6 bolts, 6 strut nuts, and 2 L-brackets to complete H-frame
- Hot-dip galvanized and UV stabilized for long lasting performance
- Accepts standard strut channels



SPECIFICATIONS

Table 1/3						
Catalog Number	Article Number	E- Number	Material	Temperature	Static Load Safety Factor	Rooftop Interface
PHK	360420	1319792	Polypropylene, Polyethylene	-34.4 to 54 °C	3:1	Foam

Table 2/3						
Catalog Number	Article Number	E-Number	Strut Type	Height (H)	Length (L)	Width (W)
PHK	360420	1319792	A (41 x 41 mm)	117 mm	314mm	314 mm

Table 3/3				
Catalog Number	Article Number	E-Number	Surface Area	Static Load
PHK	360420	1319792	0.18m²	6670N

ADDITIONAL PRODUCT DETAILS

Static load represents 750 lb (3,335 N) per post base. The end user must select and evaluate the strut framing to ensure the assembled H-frame can properly support the applied load.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
 Option 1 – Customer Care
 Option 2 – Technical Support

Europe

Netherlands:
 +31 800-0200135
 France:
 +33 800 901 793

Europe

Germany:
 800 1890272
 Other Countries:
 +31 13 5835404

APAC

Shanghai:
 + 86 21 2412 1618/19
 Sydney:
 +61 2 9751 8500

