



	ΔR^a can be combined		ΔR^a combination not recommended	
Surface ≥ 20		-	+	+
Surface ≥ 20		+	network for Plastic (if necessary)	network for Plastic (if necessary)
Surface ≥ 20		+	network for Plastic	+
Surface ≥ 20		+	+	-
Surface ≥ 20		+	+	-
Surface ≥ 20		+	+	-
Surface ≥ 20		+	+	-
Surface ≥ 20		+	+	-
Surface ≥ 20		+	+	-
Surface ≥ 20		+	+	-
Surface ≥ 20		+	+	-
Surface ≥ 20		+	+	-
Surface ≥ 20		+	+	-
Surface ≥ 20		+	+	-
Surface ≥ 20		+	+	-
Surface ≥ 20		+	+	-
Surface ≥ 20		+	+	-
Surface ≥ 20		+	+	-
Surface ≥ 20		+	+	-
Surface ≥ 20		+	+	-
Surface ≥ 20		+	+	-
Surface ≥ 20		+	+	-
Surface ≥ 20		+	+	-
Surface ≥ 20		+	+	-
Surface ≥ 20		+	+	-
Surface ≥ 20		+	+	-
Surface ≥ 20		+	+	-
Surface ≥ 20		+	+	-
Surface ≥ 20		+	+	-
Surface ≥ 20		+	+	-
Surface ≥ 20		+	+	-
Surface ≥ 20		+	+	-
Surface ≥ 20		+	+	-
Surface ≥ 20		+	+	-
Surface ≥ 20		+	+	-
Surface ≥ 20		+	+	-
Surface ≥ 20		+	+	-
Surface ≥ 20		+	+	-
Surface ≥ 20		+	+	-
Surface ≥ 20		+	+	-
Surface ≥ 20		+	+	-
Surface ≥ 20		+	+	-
Surface ≥ 20		+	+	-
Surface ≥ 20		+	+	-
Surface ≥ 20		+	+	-
Surface ≥ 20		+	+	-
Surface ≥ 20		+	+	-
Surface ≥ 20		+	+	-
Surface ≥ 20		+	+	-
Surface ≥ 20		+	+	-
Surface ≥ 20		+	+	-
Surface ≥ 20		+	+	-
Surface ≥ 20		+	+	-

34560-584

The horizontal rail, type ST enables the isolated assembly of a backplane. The isolation is done by an insulation strip.

For indirect backplane mounting with insulation strip

Standard where mechanical demands are high (H-ST)

Mounting top and bottom

< 28 HP not printed

Aluminum extrusion, anodized finish, conductive contact surface, with HP markings



PRODUCT ATTRIBUTES

Rack Width: 84HP

Package Quantity: 1

Finish: Anodized

Length: 431.8mm

Material: Aluminum

Product Family: EuropacPRO; RatiopacPRO; RatiopacPRO AIR; CompacPRO; PropacPRO

Product Type: Horizontal Rail

Type: Heavy, ST

Works With: Subracks; Cases

Net Weight: 0.13kg

*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address, parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

ADDITIONAL PRODUCT DETAILS

Delivery is in standard pack multiples. Pricing is per individual item.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff

