


# MDRCPT-2 Manual Din Rail Cutting and Punching Tool



## FEATURES

Punches slots and cuts DIN rail without burrs or deformation

Punches horizontal and vertical slots

Works with five different types of DIN rail and M6 threaded rod

Includes ruler, guide and end stops

RoHS compliant



## SPECIFICATIONS

| Catalog Number | Article Number | Material        | Slot Size    | Depth | Height | Length | Unit Weight |
|----------------|----------------|-----------------|--------------|-------|--------|--------|-------------|
| MDRCPT-2       | 559142         | Aluminum, Steel | 6.5 x 9.5 mm | 165mm | 200 mm | 100mm  | 13 kg       |

## ADDITIONAL PRODUCT DETAILS

Horizontal slots must be punched a minimum of 8 mm (0.315") from the edge of the DIN rail. Vertical slots must be punched a minimum of 12 mm (0.472") from the edge of the DIN rail.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

#### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

#### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

#### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

#### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

**CADDY**

**ERICO**

**HOFFMAN**

**ILSCO**

**SCHROFF**

**TRACHTE**