


# Steel Flange Adapter Assembly



## FEATURES

Steel Flange Adapter and Universal Structural Bracket are preassembled, limiting work required in the field

Installs on top or bottom flange of I-beams or bar joists

Low profile easily fits between metal deck and steel structure

Thumb spring retainer allows for ease of positioning

Integrated angle gauge easily displays brace member angle of installation

Snap-off bolt head helps enable easy installation and inspection of seismic sway braces

Works with 1" through 2" brace pipes to reduce inventory

Meets NFPA® 13 as pre-qualified for seismic applications

FM Approved with the following brace members: 1-2 in Sch40 Pipe

FM Specification Tested with the following brace members: 1-2 in Sch40 Pipe



## SPECIFICATIONS

Table 1/2

| Catalog Number | Article Number | Material | Finish            | Flange Thickness (FT) | Height (H) | Width (W) |
|----------------|----------------|----------|-------------------|-----------------------|------------|-----------|
| CSBS1A         | 404505         | Steel    | Electrogalvanized | 6 - 19 mm             | 67 mm      | 92 mm     |



Table 2/2

| Catalog Number | Article Number | Angle (a) | A      | B     | C     | D     |
|----------------|----------------|-----------|--------|-------|-------|-------|
| CSBS1A         | 404505         | 45 °      | 105 mm | 33 mm | 65 mm | 23 mm |

| UL Loads    |                  |                         |             |
|-------------|------------------|-------------------------|-------------|
| Part Number | Flange Thickness | Brace Member            | Load Rating |
| CSBS1A      | 6 - 8 mm         | DN25 - DN50 Sch. 40 NPS | 6672 N      |
|             | 8 - 19 mm        |                         | 7561 N      |

| FM Loads    |                                                          |           |           |           |                       |           |           |           |
|-------------|----------------------------------------------------------|-----------|-----------|-----------|-----------------------|-----------|-----------|-----------|
| Part Number | Horizontal Capacity per Installation Angle from Vertical |           |           |           |                       |           |           |           |
|             | Perpendicular to Structure                               |           |           |           | Parallel to Structure |           |           |           |
|             | 30° - 44°                                                | 45° - 59° | 60° - 74° | 75° - 90° | 30° - 44°             | 45° - 59° | 60° - 74° | 75° - 90° |
| CSBS1A      | 3780 N                                                   | 7910 N    | 12320 N   | 12630 N   | 3910 N                | 6360 N    | 8980 N    | 10720 N   |

## DIAGRAMS



## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

### Europe

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

### Europe

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

### APAC

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**

