


# RackChiller CDU40 Coolant Distribution Unit

## Data Solutions



The nVent HOFFMAN RackChiller CDU40 is a rack-based Coolant Distribution Unit (CDU), built for the needs of today's most demanding HPC requirements. Capable of managing 40kW+ of heat load in a remarkably small 4U of space. The RackChiller CDU40 is an extremely efficient heat exchanger that uses ASHRAE W4 warm water to manage processor and component heat.

### INDUSTRY STANDARDS

UR/cUR Recognized

CE

### FEATURES

Manages 40kW+ of processor load per network

Compatible with ASHRAE W4 warm water cooling

N+1 redundant centralized pumps

Dry-break quick disconnects (optional)

5-inch LCD screen with touch functionality

Integrated control and monitoring system (Webserver, Modbus, SNMP)

Internal and external leak detection system

4U rack-mount chassis

Warm water cooling reduces the need for chillers

Quick and easy installation and service

Pump redundancy: 3 pumps for n+1 redundancy



### SPECIFICATIONS

| Table 1/3      |                |            |           |           |            |        |
|----------------|----------------|------------|-----------|-----------|------------|--------|
| Catalog Number | Article Number | Height (H) | Width (W) | Depth (D) | Material   | Finish |
| CDU0402R001    | 57118          | 177mm      | 430mm     | 994mm     | Mild Steel | Plated |
| CDU0402R001Q   | 57117          | 177mm      | 430mm     | 994mm     | Mild Steel | Plated |

| Table 2/3      |                |           |            |        |               |                 |
|----------------|----------------|-----------|------------|--------|---------------|-----------------|
| Catalog Number | Article Number | Color     | Color Code | Volume | Rated Voltage | Rated Frequency |
| CDU0402R001    | 57118          | Jet Black | RAL 9005   | 9.5l   | 100 – 240V    | 50 – 60Hz       |
| CDU0402R001Q   | 57117          | Jet Black | RAL 9005   | 9.5l   | 100 – 240V    | 50 – 60Hz       |

| Table 3/3      |                |                          |                         |
|----------------|----------------|--------------------------|-------------------------|
| Catalog Number | Article Number | Rated Load Current Range | Type                    |
| CDU0402R001    | 57118          | 2.47 – 4.44A             | Unfilled, with Triclamp |
| CDU0402R001Q   | 57117          | 2.47 – 4.44A             | Filled, with CGB20      |

## DIAGRAMS



## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**