

Insertor/Extractor Handle Type IET, Black Lever, Grey Button, Bottom, 100 Pieces

CATALOG NUMBER

20817-707

The inserter/extractor handle, type IET in accordance with IEEE 1101.10. 0.1" offset. Two of these handles can overcome a single lever force of 700 N (per pair).

FEATURES

Suitable for insertion and extraction forces up to 700 N (per pair)

In accordance with IEEE 1101.10 and IEC 60297-3-102

A microswitch can be mounted

0.1" offset is used for PSUs with SMD Plus



PRODUCT ATTRIBUTES

Package Quantity: 100

Handle Type: IET; Bottom Front

Flammability Rating: UL® 94V-0

Color: Black

Complies With: EN 45545-2

Height (H): 232mm

Material: Polycarbonate; Zinc Alloy

Product Type: Handle

Type: Insertor/Extractor, 0.1" Offset

Works With: Front Panels

Net Weight: 2.278kg

*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address, parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

Please order Coding pegs and Microswitch separately.

Technical drawing of a 26mm wide door handle. The drawing includes a perspective view, a top view, and a side view. Dimensions are in mm.

- Perspective View:** Shows the handle with a mounting plate and a screw. Dimensions include 6.61 (height of the mounting plate) and 2.54 (width of the handle).
- Top View:** Shows the handle from above. Dimensions include 20 (width of the mounting plate), 2.54 (width of the handle), 7.62 (width of the mounting plate), and 2.54 (width of the handle).
- Side View:** Shows the handle from the side. Dimensions include 2.5 (width of the mounting plate), 6.1 (height of the mounting plate), 14 (width of the mounting plate), 3.6 (width of the handle), 2.5 (width of the handle), 3.8 (width of the handle), 45 (height of the handle), 12.75 (width of the handle), 22.75 (width of the handle), 8.15 (width of the handle), 8.55 (width of the handle), and Ø 2.95 (diameter of the handle).

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff

