

300M Universal Beam Clamp



FEATURES

Universal beam clamp for standard beams

Structural attachment (with infinite adjustment) to top or bottom flange of metal beams to support hanger rod

Including set screw and lock nut

Material: Cast Iron
Finish: Electrogalvanized



SPECIFICATIONS

Table 1/2

Catalog Number	Article Number	E-Number	Hole Type	Hole Size (HS)	Thread Size (TS)	Flange Thickness (FT)
30009MM	389500	1341201	Plain	9 mm		18 mm Max
30011MM	389510	1341203	Plain	11 mm		20 mm Max
30013MM	389520	1341205	Plain	13 mm		26 mm Max
30017MM	389505	3535827	Plain	17 mm		28 mm Max
300M10	386820	1341204	Threaded		M10	20 mm Max
300M12	386830	1341206	Threaded		M12	26 mm Max
300M6	386805	1341200	Threaded		M6	18 mm Max
300M8	386810	1341202	Threaded		M8	18 mm Max


Table 2/2

Catalog Number	Article Number	E-Number	A	Torque (TQ)	Static Load	Certifications
30009MM	389500	1341201	21 mm	14 N·m Min	1200N	ITB, VdS G4005005
30011MM	389510	1341203	23 mm	14 N·m Min	2500N	VdS G4005005, FM Approved, Pipe Hanger Components, ITB
30013MM	389520	1341205	35 mm	14 N·m Min	3500N	FM Approved, Pipe Hanger Components, VdS G4913044, ITB
30017MM	389505	3535827	30 mm	14 N·m Min	5500N	FM Approved, Pipe Hanger Components, ITB, VdS G4031026
300M10	386820	1341204	23 mm	14 N·m Min	2500N	VdS G4005005, FM Approved, Pipe Hanger Components, ITB
300M12	386830	1341206	35 mm	14 N·m Min	3500N	ITB, VdS G4913044, FM Approved, Pipe Hanger Components
300M6	386805	1341200	21 mm	14 N·m Min	1200N	
300M8	386810	1341202	21 mm	14 N·m Min	1200N	ITB, VdS G4005005

ADDITIONAL PRODUCT DETAILS

Setscrew must be tightened and torqued onto the sloped side of the I-beam.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

