

Flanged Drop-in Anchor



FEATURES

Internal thread provides easy removal and serviceability

Installs flush for standard embedment

Suitable for redundant non-structural systems on cracked and non-cracked concrete

Fire resistance class R30-R120 for design of anchorages under exposure to fire

Lip makes the flush installation easier by helping achieve consistent anchor depth and easy threaded rod alignment

Material: Steel
Finish: Electrogalvanized




SPECIFICATIONS

Catalog Number	Article Number	E-Number	Hole Size (HS)	Length (L)	Drill Bit Diameter (Ø)	Certifications
LAM1040	574420	1305787	10 mm	40mm	12 mm	CE, 14-0068, VdS, CE, 14-0135
LAM1250	574430	1305788	12 mm	50mm	15 mm	CE, 14-0068, VdS, CE, 14-0135
LAM625	589890	1305789	6 mm	25mm	8 mm	CE, 14-0135, CE, 14-0068
LAM830	574410	1305786	8 mm	30mm	10 mm	CE, 14-0068, CE, 14-0135, VdS

Characteristic Axial Loads from ETA 14-0135			
Part Number	Cracked Concrete C20/25	Non-Cracked Concrete C20/25	Standard Embedment Depth
LAM625	-	2.44 kN	25 mm
LAM830	-	3.21 kN	30 mm
LAM1040	-	4.23 kN	40 mm
LAM1250	-	5.92 kN	50 mm

Characteristic Axial Loads from ETA 14-0068 - for redundant non-structural systems			
Part Number	Cracked Concrete C20/25	Non-Cracked Concrete C20/25	Standard Embedment Depth
LAM625	0.80 kN	0.80 kN	25 mm
LAM830	1.20 kN	1.20 kN	30 mm
LAM1040	1.70 kN	1.70 kN	40 mm
LAM1250	2.60 kN	2.60 kN	50 mm

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

