

nVent CADDY Speed Link SLS with Hook



FEATURES

Complete system includes wire, locking device and pre-assembled hook end fitting

Hooks to a wide range of nVent CADDY fasteners

Fastens to the building structure or hanging services by looping around and hooking to wire rope

Easy to remove for applications requiring maintenance

Spring latch helps provide secure connection

Insert cable through hole and use bottom side of hook as an end stop

Finger tightening of nut secures the locking device into position without tools

Installs in strut profiles without the need to insert fingers or tools into the strut

Material: Steel;Zinc Alloy;Polypropylene
Finish: Electrogalvanized
Static Load Safety Factor: 5:1
Complies With: SMACNA HVAC-DCS



SPECIFICATIONS

Table 1/3

Catalog Number	Article Number	E-Number	Wire Rope Diameter	Wire Rope Length	A	B
SLS2L1	196741	1319684	2 mm	1m	57 mm	20 mm
SLS2L10	196746	1319689	2 mm	10m	57 mm	20 mm
SLS2L2	196742	1319685	2 mm	2m	57 mm	20 mm
SLS3L10	196752	1319695	3 mm	10m	57.6 mm	23.2 mm
SLS3L3	196749	1319692	3 mm	3m	57.6 mm	23.2 mm
SLS3L5	196750	1319693	3 mm	5m	57.6 mm	23.2 mm

Table 2/3

Catalog Number	Article Number	E-Number	C	Height 1 (H1)	Height 2 (H2)	Thread Size (TS)
SLS2L1	196741	1319684	5.5 mm	53mm	43.5mm	M8
SLS2L10	196746	1319689	5.5 mm	53mm	43.5mm	M8

Catalog Number	Article Number	E-Number	C	Height 1 (H1)	Height 2 (H2)	Thread Size (TS)
SLS2L2	196742	1319685	5.5 mm	53mm	43.5mm	M8
SLS3L10	196752	1319695	6.1 mm	53mm	46.5mm	M12
SLS3L3	196749	1319692	6.1 mm	53mm	46.5mm	M12
SLS3L5	196750	1319693	6.1 mm	53mm	46.5mm	M12

Table 3/3

Catalog Number	Article Number	E-Number	Width (W)	Hole Size (HS)	Slot Size (SS)	Thickness (T)	Static Load
SLS2L1	196741	1319684	16 mm	8 - 10 mm	8 x 6.5 mm - 8 x 10 mm	4 mm Max	270N
SLS2L10	196746	1319689	16 mm	8 - 10 mm	8 x 6.5 mm - 8 x 10 mm	4 mm Max	270N
SLS2L2	196742	1319685	16 mm	8 - 10 mm	8 x 6.5 mm - 8 x 10 mm	4 mm Max	270N
SLS3L10	196752	1319695	20 mm	12 - 14 mm	12 x 10 mm - 12 x 14 mm	6 mm Max	670N
SLS3L3	196749	1319692	20 mm	12 - 14 mm	12 x 10 mm - 12 x 14 mm	6 mm Max	670N
SLS3L5	196750	1319693	20 mm	12 - 14 mm	12 x 10 mm - 12 x 14 mm	6 mm Max	670N



ADDITIONAL PRODUCT DETAILS


The 2 mm locking device is compatible with C-Channel Types E0 and E0L.

The 3 mm locking device is compatible with C-Channel Types E1, E2, E2L, E3, E4, E5, Strut Channel Type C, Slotted, Strut Channel Type A, Slotted, Strut Channel Type AS, Perforated, Strut Channel Type CC, Slotted, Strut Channel Type AA, Slotted.

Total load per wire on a multi-tier trapeze must not exceed static load.

DIAGRAMS





WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

