

SIT CLIM Insulated Pipe Clamp with Rubber Ends



FEATURES

Pre-mounted with steel two screw pipe clamp

Fire rating B2 acc. to DIN 4102-1

Fire rating M1 acc. to NFP 92-501

Material:	Steel;Polyisocyanurate
Finish:	Electrogalvanized
Density:	80 kg/m ³
Compressive Strength:	520 kPa @ 23 °C
Thermal Conductivity:	0.03 W/m-K @ 10 °C
Temperature:	-40 to 90 °C

SPECIFICATIONS

Table 1/2

Catalog Number	Article Number	E-Number	Insulation Thickness	Outer Diameter (OD)	NB/D N	Rod Size (RS)	B
SCLI13I0010	580091	3535491	13 mm	10 mm		M8, M10	50 mm
SCLI13I0012	580092	3535492	13 mm	12 mm		M8, M10	50 mm
SCLI13I0016	580093	3535493	13 mm	15 mm		M8, M10	50 mm
SCLI13I0018	580105	3535494	13 mm	18 mm		M8, M10	50 mm


Catalog Number	ArticleNumber	E- Number	Insulation Thickness	Outer Diameter (OD)	NB/D N	Rod Size(RS)	B
SCLI13I0022	580111	3535495	13 mm	22 mm		M8, M10	50 mm
SCLI13I0027	580120	3532976	13 mm	27 mm	20	M8, M10	50 mm
SCLI13I0028	580121	3535497	13 mm	28 mm		M8, M10	50 mm
SCLI13I0034	580130	3532978	13 mm	34 mm	25	M8, M10	50 mm
SCLI13I0035	580135	3535499	13 mm	35 mm		M8, M10	50 mm
SCLI13I0042	580140	3532981	13 mm	42 mm	32	M8, M10	50 mm
SCLI13I0049	580150	3532983	13 mm	49 mm	40	M8, M10	50 mm
SCLI13I0054	580151	3535502	13 mm	54 mm		M8, M10	50 mm
SCLI13I0060	580160	3532985	13 mm	60 mm	50	M8, M10	50 mm
SCLI13I0076	581610	3532989	13 mm	76 mm	65	M8, M10	50 mm
SCLI13I0089	581620	3532992	13 mm	89 mm	80	M8, M10	50 mm
SCLI13I0108	581640	3532996	13 mm	108 mm		M8, M10	50 mm
SCLI19I0010	580270	3535511	19 mm	10 mm		M8, M10	50 mm
SCLI19I0012	580280	3535512	19 mm	12 mm		M8, M10	50 mm
SCLI19I0016	580290	3535513	19 mm	15 mm		M8, M10	50 mm
SCLI19I0018	580305	3535514	19 mm	18 mm		M8, M10	50 mm

Table 2/2

Catalog Number	Article Number	E- Number	Insulation Thickness	Outer Diameter (OD)	NB/D N	Rod Size (RS)	B
SCLI19I0021	580310	3533014	19 mm	21 mm	15	M8, M10	50 mm
SCLI19I0022	580311	3535515	19 mm	22 mm		M8, M10	50 mm
SCLI19I0027	580320	3533016	19 mm	27 mm	20	M8, M10	50 mm
SCLI19I0028	580321	3535517	19 mm	28 mm		M8, M10	50 mm
SCLI19I0034	580330	3533018	19 mm	34 mm	25	M8, M10	50 mm
SCLI19I0035	580335	3535519	19 mm	35 mm		M8, M10	50 mm
SCLI19I0042	580340	3533021	19 mm	42 mm	32	M8, M10	50 mm
SCLI19I0049	580350	3533023	19 mm	49 mm	40	M8, M10	50 mm
SCLI19I0054	580351	3535522	19 mm	54 mm		M8, M10	50 mm

Catalog Number	ArticleNumber	E- Number	Insulation Thickness	Outer Diameter (OD)	NB/D N	Rod Size(RS)	B
SCLI19I0060	580360	3533025	19 mm	60 mm	50	M8, M10	50 mm
SCLI19I0076	581670	3533029	19 mm	76 mm	65	M8, M10	50 mm
SCLI19I0089	581680	3533032	19 mm	89 mm	80	M8, M10	50 mm
SCLI19I0108	581700	3533036	19 mm	108 mm		M8, M10	50 mm
SCLI19I0114	581710	3533038	19 mm	114 mm	100	M8, M10	50 mm
SCLI19I0139	581725	3535527	19 mm	139.7 mm	125	M8, M10	50 mm
SCLI19I0168	581735	3535528	19 mm	168.3 mm	150	M8, M10	50 mm

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

