

Strut Nut without Spring

FEATURES

Used to create metal frames with nVent CADDY Eristrut channels





Static Load Safety Factor: 3:1

SPECIFICATIONS

Catalog Number	Article Number	E-Number	Material	Finish	Rod Size (RS)	Thickness (T)	Torque (TQ)
NUTM10EG	315025	1342863	Steel	Electrogalvanized	10	8 mm	55 N·m
NUTM10HD	315020	1340552	Steel	Hot-Dip Galvanized	10	8 mm	55 N·m
NUTM10S6	315160	1342864	Stainless Steel 316 (EN 1.4401)		10	8 mm	55 N·m
NUTM12EG	315035	1342865	Steel	Electrogalvanized	12	8 mm	55 N·m
NUTM12HD	315030	1340553	Steel	Hot-Dip Galvanized	12	8 mm	55 N·m
NUTM12S6	315170	1342866	Stainless Steel 316 (EN 1.4401)		12	8 mm	55 N·m
NUTM16EG	315036	3435674	Steel	Electrogalvanized	16	11.7 mm	125 N·m
NUTM16HD	315037	3535489	Steel	Hot-Dip Galvanized	16	11.7 mm	125 N·m

Catalog Number	Article Number	E- Number	Material	Finish	Rod Size (RS)	Thickness (T)	Torque (TQ)
NUTM6EG	314995	1342859	Steel	Electrogalvanized	6	6 mm	12 N·m
NUTM6HD	315000	1340550	Steel	Hot-Dip Galvanized	6	6 mm	12 N·m
NUTM6S6	315140	1342860	Stainless Steel 316 (EN 1.4401)		6	6 mm	12 N·m
NUTM8EG	315015	1342861	Steel	Electrogalvanized	8	6 mm	28 N·m
NUTM8HD	315010	1340551	Steel	Hot-Dip Galvanized	8	6 mm	28 N·m
NUTM8S6	315150	1342862	Stainless Steel 316 (EN 1.4401)		8	6 mm	28 N·m

Pull-Out Strength				
Part Number	Channel Type	Channel Thickness		
		2,5 mm	2 mm	1,5 mm
NUTM6xx	A, C	2000 N	2000 N	2000 N
	D, E	2000 N	-	-
NUTM8xx	A, C	3330 N	3330 N	3330 N
	D, E	3330 N	-	-
NUTM10xx	A, C	4890 N	4440 N	4440 N
	D, E	4890 N	-	-
NUTM12xx	A, C	4890 N	4660 N	4440 N
	D, E	3670 N	-	-
NUTM12Txx	A	5670 N	5050 N	4440 N
	D, E	4250 N	-	-
NUTM16xx	A	5670 N	4660 N	4440 N
	D, E	4250 N	-	-



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

