

# 6", DN150 Pipe/Conduit Rigid Quick Grip Lateral Sway Brace, electrogalvanized

## CATALOG NUMBER

**CSBQG0600EG**



The Quick Grip Lateral Brace, part of the nVent CADDY line of fire sprinkler bracing systems from nVent, is designed to help simplify installations when bracing service pipe for seismic or other catastrophic events. It features an innovative design for quick attachment of brace pipe to service pipe saving time and money.

## FEATURES

Easy two-step installation eliminates extra trips between structure and service pipe

Works with 1" and 1 1/4" (25 mm and 32 mm) brace pipes to reduce inventory

Yellow tips provide a visual indicator that the bolts have been properly torqued

Easy installation with an impact wrench from the bottom side of the clamp

Meets NFPA®-13 requirements for seismic sway bracing

Meets CEN/TS 17551:2021 requirements for Seismic Sway Bracing



## PRODUCT ATTRIBUTES

Article Number: 404472

Material: Steel

Finish: Electrogalvanized

Pipe Size: 6"

NB/DN: 150

Height (H): 235.50 - 244.9 mm

Width (W): 298 mm

| FM Loads                     |                         |                                                          |          |          |          |
|------------------------------|-------------------------|----------------------------------------------------------|----------|----------|----------|
| Part Number                  | Service Pipe Schedule   | Lateral                                                  |          |          |          |
|                              |                         | Horizontal Capacity per Installation Angle from Vertical |          |          |          |
|                              |                         | 30°- 44°                                                 | 45°- 59° | 60°- 74° | 75°- 90° |
| CSBQG0250EG/<br>CSBQG0250MEG | EN10255 L (Lightwall)   | 6270 N                                                   | 8895 N   | 10900 N  | 12190 N  |
|                              | EN10255 M (10)          | 6270 N                                                   | 8895 N   | 10900 N  | 12190 N  |
|                              | EN10255 H (40)          | 6270 N                                                   | 8895 N   | 10900 N  | 12190 N  |
| CSBQG0300EG                  | EN10255 L (Lightwall)   | 5295 N                                                   | 7475 N   | 9163 N   | 10230 N  |
|                              | EN10255 M (10)          | 5295 N                                                   | 7475 N   | 9163 N   | 10230 N  |
|                              | EN10255 H (40)          | 5295 N                                                   | 7475 N   | 9163 N   | 10230 N  |
| CSBQG0400EG                  | EN10255 L (Lightwall)   | 5295 N                                                   | 7475 N   | 9163 N   | 10230 N  |
|                              | EN10255 M (10)          | 5295 N                                                   | 7475 N   | 9163 N   | 10230 N  |
|                              | EN10255 H (40)          | 5295 N                                                   | 7475 N   | 9163 N   | 10230 N  |
| CSBQG0600EG                  | EN10255 L (Lightwall)   | 3870 N                                                   | 5470 N   | 6715 N   | 7515 N   |
|                              | EN10255 M (10)          | 3870 N                                                   | 5470 N   | 6715 N   | 7515 N   |
|                              | EN10255 H (40)          | 4315 N                                                   | 6095 N   | 7475 N   | 8320 N   |
| CSBQG0800EG                  | 4.8 mm (Wall Thickness) | 3515 N                                                   | 4940 N   | 6050 N   | 6760 N   |
|                              | EN10255 H (40)          | 3515 N                                                   | 4940 N   | 6050 N   | 6760 N   |

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

#### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

#### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

#### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

#### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

