

nVent CADDY Cushion Clamp Insulated Strut Clamp for Pipe/Tube



FEATURES

Fits into open side of strut channel

Plastic cushion is hinged to spread apart for easy installation

Reduces noise and absorbs shock by gripping the pipe/tube firmly

Square neck of carriage bolt prevents over-tightening

Nylon locknut prevents loosening under vibration

FM® Specification Tested (from 3/8" to 4" of Copper Tube Size)

Material: Steel; Polypropylene

Finish: Zinc Chromate





SPECIFICATIONS

Catalog Number	Article Number	Outer Diameter (OD)	Copper Tube Size	NB/DN	Width (W)	A	B
CCC0037	598883	9.5 mm	1/4"		39.7 mm	18.9 mm	35.4 mm
CCC0050	598884	12.7 mm	3/8"	8	39.7 mm	22.1 mm	38.6 mm
CCC0062	598886	15.8 mm	1/2"	10	39.7 mm	25.2 mm	41.7 mm
CCC0075	598888	19.1 mm	5/8"		39.7 mm	28.4 mm	44.9 mm
CCC0087	598891	22.2 mm	3/4"	15	39.7 mm	31.6 mm	48.1 mm
CCC0100	598892	25.4 mm		20	39.7 mm	34.8 mm	51.3 mm
CCC0112	598894	28.6 mm	1"		39.7 mm	39 mm	62.4 mm
CCC0125	598895	31.8 mm		25	39.7 mm	42.1 mm	65.6 mm
CCC0162	598899	41.3 mm	1 1/2"	32	39.7 mm	51.6 mm	75.1 mm
CCC0187	598903	47.6 mm		40	39.7 mm	59 mm	81.5 mm
CCC0212	598906	53.9 mm	2"		39.7 mm	68.5 mm	91 mm

Catalog Number	Article Number	Outer Diameter (OD)	Copper Tube Size	NB/DN	Width (W)	A	B
CCC0237	598908	60.3 mm		50	39.7 mm	74.9 mm	97.4 mm
CCC0450	598957	114.3 mm		100	39.7 mm	132 mm	160.5 mm

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
 Option 1 – Customer Care
 Option 2 – Technical Support

Europe

Netherlands:
 +31 800-0200135
 France:
 +33 800 901 793

Europe

Germany:
 800 1890272
 Other Countries:
 +31 13 5835404

APAC

Shanghai:
 + 86 21 2412 1618/19
 Sydney:
 +61 2 9751 8500

