

# Copper-Bonded Ground Rod, Threaded



## FEATURES

Cold-rolled threads with continuous, unbroken grain flows preserve copper coating and are stronger than cut threads

99.9% pure electrolytic copper coating

Rods have a high carbon steel core and tip that provide superior strength when driving

Copper coating will not crack when bent or tear when driven

Minimum copper coating of 10 mils on rods listed to UL® 467

nVent ERICO name, length, diameter and part number is roll-stamped within 12" (304,8 mm) of chamfered end

UL logo and control number where applicable stamped on each rod for easy inspection after installation

**Tensile Strength:** 552 MPa Min  
**Material:** Copper-Bonded Steel  
**Thread Location:** Pointed and Chamfered Ends



## SPECIFICATIONS

Table 1/2

| Catalog Number | Article Number | Ground Rod Diameter, Nominal | Ground Rod Diameter, Actual (Ø) | Thread Size (TS) | Length (L) | Plating Thickness |
|----------------|----------------|------------------------------|---------------------------------|------------------|------------|-------------------|
| 631303         |                | 1/2"                         | 12.8 mm                         | 9/16" UNC        | 3m         | 330µm             |
| 631340         |                | 1/2"                         | 12.8 mm                         | 9/16" UNC        | 1.2m       | 254µm             |
| 631300         |                | 1/2"                         | 12.8 mm                         | 9/16" UNC        | 3m         | 254µm             |
| 631380         |                | 1/2"                         | 12.8 mm                         | 9/16" UNC        | 2.4m       | 254µm             |
| 631360         |                | 1/2"                         | 12.8 mm                         | 9/16" UNC        | 1.8m       | 254µm             |
| 631350         |                | 1/2"                         | 12.8 mm                         | 9/16" UNC        | 1.5m       | 254µm             |
| 6358660        |                | 5/8"                         | 14.2 mm                         | 5/8" UNC         | 2m         | 254µm             |
| 635880         | 635880         | 5/8"                         | 14.2 mm                         | 5/8" UNC         | 2.4m       | 254µm             |
| 635800         |                | 5/8"                         | 14.2 mm                         | 5/8" UNC         | 3m         | 254µm             |
| 635840         |                | 5/8"                         | 14.2 mm                         | 5/8" UNC         | 1.2m       | 254µm             |

| Catalog Number | Article Number | Ground Rod Diameter, Nominal | Ground Rod Diameter, Actual (Ø) | Thread Size (TS) | Length (L) | Plating Thickness |
|----------------|----------------|------------------------------|---------------------------------|------------------|------------|-------------------|
| 635883         |                | 5/8"                         | 14.2 mm                         | 5/8" UNC         | 2.4m       | 330µm             |
| 635850         |                | 5/8"                         | 14.2 mm                         | 5/8" UNC         | 1.5m       | 254µm             |
| 635803         |                | 5/8"                         | 14.2 mm                         | 5/8" UNC         | 3m         | 330µm             |
| 635870         |                | 5/8"                         | 14.2 mm                         | 5/8" UNC         | 2.1m       | 254µm             |
| 635860         |                | 5/8"                         | 14.2 mm                         | 5/8" UNC         | 1.8m       | 254µm             |
| 635830         |                | 5/8"                         | 14.2 mm                         | 5/8" UNC         | 0.9m       | 254µm             |
| 635843         |                | 5/8"                         | 14.2 mm                         | 5/8" UNC         | 1.2m       | 330µm             |
| 633450         |                | 3/4"                         | 17.3 mm                         | 3/4" UNC         | 1.5m       | 254µm             |
| 633480         | 633480         | 3/4"                         | 17.3 mm                         | 3/4" UNC         | 2.4m       | 254µm             |
| 6334330        |                | 3/4"                         | 17.3 mm                         | 3/4" UNC         | 1m         | 254µm             |

Table 2/2

| Catalog Number | Article Number | Ground Rod Diameter, Nominal | Ground Rod Diameter, Actual (Ø) | Thread Size (TS) | Length (L) | Plating Thickness |
|----------------|----------------|------------------------------|---------------------------------|------------------|------------|-------------------|
| 633463         |                | 3/4"                         | 17.3 mm                         | 3/4" UNC         | 1.8m       | 330µm             |
| 633460         |                | 3/4"                         | 17.3 mm                         | 3/4" UNC         | 1.8m       | 254µm             |
| 633470         |                | 3/4"                         | 17.3 mm                         | 3/4" UNC         | 2.1m       | 254µm             |
| 633440         |                | 3/4"                         | 17.3 mm                         | 3/4" UNC         | 1.2m       | 254µm             |
| 633400         |                | 3/4"                         | 17.3 mm                         | 3/4" UNC         | 3m         | 254µm             |
| 633430         |                | 3/4"                         | 17.3 mm                         | 3/4" UNC         | 0.9m       | 254µm             |
| 633415         |                | 3/4"                         | 17.3 mm                         | 3/4" UNC         | 4.6m       | 254µm             |
| 633403         |                | 3/4"                         | 17.3 mm                         | 3/4" UNC         | 3m         | 330µm             |
| 634400         |                | 1"                           | 23.2 mm                         | 1" UNC           | 3m         | 254µm             |

Table 1/2

| Catalog Number | Article Number | Unit Weight | Complies With                    | Certifications            |
|----------------|----------------|-------------|----------------------------------|---------------------------|
| 631303         |                | 3.2 kg      | ANSI®/NEMA® GR1                  | cUL, UL                   |
| 631340         |                | 1.2 kg      |                                  |                           |
| 631300         |                | 3.1 kg      | ANSI®/NEMA® GR1                  | CSA-US, CSA, UL, cUL      |
| 631380         |                | 2.4 kg      | ANSI®/NEMA® GR1                  | UL                        |
| 631360         |                | 1.9 kg      |                                  |                           |
| 631350         |                | 1.6 kg      |                                  |                           |
| 6358660        |                | 2.48 kg     | IEC® EN 62561-2                  |                           |
| 635880         | 635880         | 3 kg        | ANSI®/NEMA® GR1, IEC® EN 62561-2 | RUS, UL                   |
| 635800         |                | 3.8 kg      | ANSI®/NEMA® GR1, IEC® EN 62561-2 | CSA, RUS, CSA-US, cUL, UL |
| 635840         |                | 1.5 kg      | IEC® EN 62561-2                  |                           |

| Catalog Number | Article Number | Unit Weight | Complies With                    | Certifications |
|----------------|----------------|-------------|----------------------------------|----------------|
| 635883         |                | 3 kg        | ANSI®/NEMA® GR1, IEC® EN 62561-2 | RUS, UL        |
| 635850         |                | 1.9 kg      | IEC® EN 62561-2                  |                |
| 635803         |                | 3.9 kg      | ANSI®/NEMA® GR1, IEC® EN 62561-2 | RUS, UL, cUL   |
| 635870         |                | 2.9 kg      | IEC® EN 62561-2                  |                |
| 635860         |                | 2.3 kg      | IEC® EN 62561-2                  |                |
| 635830         |                | 1.2 kg      | IEC® EN 62561-2                  |                |
| 635843         |                | 1.5 kg      | IEC® EN 62561-2                  |                |
| 633450         |                | 2.8 kg      | IEC® EN 62561-2                  |                |
| 633480         | 633480         | 4.4 kg      | ANSI®/NEMA® GR1, IEC® EN 62561-2 | UL, RUS        |
| 6334330        |                | 2.79 kg     | IEC® EN 62561-2                  |                |


Table 2/2

| Catalog Number | Article Number | Unit Weight | Complies With                    | Certifications            |
|----------------|----------------|-------------|----------------------------------|---------------------------|
| 633463         |                | 3.2 kg      | IEC® EN 62561-2                  |                           |
| 633460         |                | 3.2 kg      | IEC® EN 62561-2                  |                           |
| 633470         |                | 3.9 kg      | IEC® EN 62561-2                  |                           |
| 633440         |                | 2.2 kg      | IEC® EN 62561-2                  |                           |
| 633400         |                | 5.7 kg      | ANSI®/NEMA® GR1, IEC® EN 62561-2 | UL, cUL, RUS, CSA-US, CSA |
| 633430         |                | 1.7 kg      | IEC® EN 62561-2                  |                           |
| 633415         |                | 8.5 kg      | ANSI®/NEMA® GR1, IEC® EN 62561-2 | UL, cUL                   |
| 633403         |                | 5.7 kg      | ANSI®/NEMA® GR1, IEC® EN 62561-2 | cUL, UL                   |
| 634400         |                | 10 kg       | ANSI®/NEMA® GR1                  | CSA-US, UL, cUL, CSA      |

## ADDITIONAL PRODUCT DETAILS

For rods to be listed to UL® 467, they must be at least 8' (2.44 m) in length.

IEC® EN 62561-2 supercedes EN 50164-2.



## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

⚠ WARNING: This product can expose you to chemicals including nickel, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov).

#### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

#### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

#### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

#### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

**CADDY**

**ERICO**

**HOFFMAN**

**ILSCO**

**SCHROFF**

**TRACHTE**