

Roof Mount Air Conditioner, DEK



This roof cooling unit, DEK, with a IP54 protection degree, provides cooling, either to one enclosure or to a complete assembly, depending on the cooling requirements and desired energy consumption level. It is placed on top of the enclosure and is perfect when there is not enough space on the door or side panels.

FEATURES

Finish: RAL 7035 for the galvanized steel versions

Temperature limits outside: +20°C to +50°C

Temperature limits inside: +20°C to +45°C

Pack quantity: 1



SPECIFICATIONS

Table 1/3

Catalog Number	E-Number	Cooling Capacity, L35L35	Cooling Capacity, L35L50	Nominal Voltage	Number of Phases	Frequency
DEK04BTU9	2506777	410W	240W	230V	1Ph	50/60 Hz
DEK04BTUB	2506778	410W	240W	230V	1Ph	50/60 Hz
DEK08BTU9	2506849	820W	680W	230V	1Ph	50/60 Hz
DEK08BTUB	2506850	820W	680W	230V	1Ph	50/60 Hz
DEK12BTU9	2506855	1150W	900W	230V	1Ph	50/60 Hz
DEK12BTUB	2506856	1150W	900W	230V	1Ph	50/60 Hz
DEK15BTU9	2506861	1550W	1200W	230V	1Ph	50/60 Hz
DEK15BTUB	2506862	1550W	1200W	230V	1Ph	50/60 Hz
DEK20BT09	2506867	2050W	1560W	230V	1Ph	50/60 Hz
DEK20BT0B	2506868	2050W	1560W	230V	1Ph	50/60 Hz
DEK20LT09	2506871	2050W	1560W	400V	3Ph	50/60 Hz
DEK20LT0B	2506872	2050W	1560W	400V	3Ph	50/60 Hz
DEK20NTU9	2506873	2050W	1560W	460V	3Ph	60 Hz
DEK20NTUB	2506874	2050W	1560W	460V	3Ph	60 Hz
DEK30BT09	2506875	2900W	2250W	230V	1Ph	50/60 Hz

Catalog Number	E-Number	Cooling Capacity, L35L35	Cooling Capacity, L35L50	Nominal Voltage	Number of Phases	Frequency
DEK30BT0B	2506876	2900W	2250W	230V	1Ph	50/60 Hz
DEK30LT09	2506877	2900W	2250W	400V	3Ph	50/60 Hz
DEK30LT0B	2506878	2900W	2250W	400V	3Ph	50/60 Hz
DEK30NTU9	2506879	2900W	2250W	460V	3Ph	60 Hz
DEK30NTUB	2506880	2900W	2250W	460V	3Ph	60 Hz

Table 2/3

Catalog Number	E-Number	Cooling Capacity, L35L35	Cooling Capacity, L35L50	Nominal Voltage	Number of Phases	Frequency
DEK40BT09	2506881	3850W	2870W	230V	1Ph	50/60 Hz
DEK40BT0B	2506882	3850W	2870W	230V	1Ph	50/60 Hz
DEK40LT09	2506883	3850W	2870W	400V	3Ph	50/60 Hz
DEK40LT0B	2506884	3850W	2870W	400V	3Ph	50/60 Hz
DEK40NTU9	2506885	3850W	2870W	460V	3Ph	60 Hz
DEK40NTUB	2506886	3850W	2870W	460V	3Ph	60 Hz
DEK04CT09	2506847	410W	240W	115V	1Ph	60 Hz
DEK04CT0B	2506848	410W	240W	115V	1Ph	60 Hz
DEK08CT09	2506851	820W	680W	115V	1Ph	50/60 Hz
DEK08CT0B	2506852	820W	680W	115V	1Ph	50/60 Hz
DEK08GT09	2506853	820W	680W	400V, 440V	2Ph	50/60 Hz
DEK08GT0B	2506854	820W	680W	400V, 440V	2Ph	50/60 Hz
DEK12CT09	2506857	1150W	900W	115V	1Ph	50/60 Hz
DEK12CT0B	2506858	1150W	900W	115V	1Ph	50/60 Hz
DEK12GT09	2506859	1150W	900W	400V, 440V	2Ph	50/60 Hz
DEK12GT0B	2506860	1150W	900W	400V, 440V	2Ph	50/60 Hz
DEK15CT09	2506863	1550W	1200W	115V	1Ph	50/60 Hz
DEK15CT0B	2506864	1550W	1200W	115V	1Ph	50/60 Hz
DEK15GT09	2506865	1550W	1200W	400V, 440V	2Ph	50/60 Hz
DEK15GT0B	2506866	1550W	1200W	400V, 440V	2Ph	50/60 Hz

Table 3/3

Catalog Number	E-Number	Cooling Capacity, L35L35	Cooling Capacity, L35L50	Nominal Voltage	Number of Phases	Frequency
DEK20CT09	2506869	2050W	1560W	115V	1Ph	50/60 Hz
DEK20CT0B	2506870	2050W	1560W	115V	1Ph	50/60 Hz

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.