

Front Panel, Front Anodized, Rear Conductive, Unshielded

Front panel, unshielded, front anodized and rear conductive.

FEATURES

Partial width front panel, Al, 2.5 mm

Al, front anodized, conductive

Depth (D):	2.5mm
Material:	Aluminum
Finish:	Anodized; Passivated
Accessory Type:	Front panel
Product Type:	Front Panel
Type:	Front Panel without Handle



SPECIFICATIONS

Table 1/3

Catalog Number	Rack Height	Rack Width	Package Quantity	Mounting	Front Finish	Rear Finish
30847-470	3U	2HP	1	Screw-on Front	Anodized	Conductive
30847-464	4U	63HP	1	Screw-on Front	Anodized	Conductive
30847-480	9U	8HP	1	Screw-on Front	Anodized	Conductive
30838-125	6U	5HP	1	Screw-on Front	Anodized	Conductive
30838-148	6U	28HP	1	Screw-on Front	Anodized	Conductive
30838-183	6U	63HP	1	Screw-on Front	Anodized	Conductive
30838-047	3U	8HP	1	Screw-on Front	Anodized	Conductive
30838-067	3U	28HP	1	Screw-on Front	Anodized	Conductive
30847-476	4U	4HP	1	Screw-on Front	Anodized	Conductive
30838-127	6U	7HP	1	Screw-on Front	Anodized	Conductive
30847-468	5U	63HP	1	Screw-on Front	Anodized	Conductive
30847-463	4U	42HP	1	Screw-on Front	Anodized	Conductive
30847-471	3U	3HP	1	Screw-on Front	Anodized	Conductive
30838-046	3U	7HP	1	Screw-on Front	Anodized	Conductive

Catalog Number	Rack Height	Rack Width	Package Quantity	Mounting	Front Finish	Rear Finish
30838-128	6U	8HP	1	Screw-on Front	Anodized	Conductive
30838-126	6U	6HP	1	Screw-on Front	Anodized	Conductive
30838-045	3U	6HP	1	Screw-on Front	Anodized	Conductive
30838-130	6U	10HP	1	Screw-on Front	Anodized	Conductive
30847-469	5U	84HP	1	Screw-on Front	Anodized	Conductive
30838-081	3U	42HP	1	Screw-on Front	Anodized	Conductive

Table 2/3

Catalog Number	Rack Height	Rack Width	Package Quantity	Mounting	Front Finish	Rear Finish
30838-123	3U	84HP	1	Screw-on Front	Anodized	Conductive
30847-460	2U	63HP	1	Screw-on Front	Anodized	Conductive
30838-141	6U	21HP	1	Screw-on Front	Anodized	Conductive
30847-462	4U	28HP	1	Screw-on Front	Anodized	Conductive
30838-132	6U	12HP	1	Screw-on Front	Anodized	Conductive
30838-044	3U	5HP	1	Screw-on Front	Anodized	Conductive
30838-043	3U	4HP	1	Screw-on Front	Anodized	Conductive
30838-136	6U		1	Screw-on Front	Anodized	Conductive
30838-134	6U	14HP	1	Screw-on Front	Anodized	Conductive
30838-102	3U	63HP	1	Screw-on Front	Anodized	Conductive
30847-467	5U	42HP	1	Screw-on Front	Anodized	Conductive
30838-053	3U	14HP	1	Screw-on Front	Anodized	Conductive
30847-459	2U	42HP	1	Screw-on Front	Anodized	Conductive
30847-556	9U	84HP	1	Screw-on Front	Anodized	Conductive
30847-458	2U	28HP	1	Screw-on Front	Anodized	Conductive
30838-055	3U	16HP	1	Screw-on Front	Anodized	Conductive
30838-162	6U	42HP	1	Screw-on Front	Anodized	Conductive
30838-204	6U	84HP	1	Screw-on Front	Anodized	Conductive
30847-484	9U	12HP	1	Screw-on Front	Anodized	Conductive
30847-465	4U	84HP	1	Screw-on Front	Anodized	Conductive

Table 3/3

Catalog Number	Rack Height	Rack Width	Package Quantity	Mounting	Front Finish	Rear Finish
30838-051	3U	12HP	1	Screw-on Front	Anodized	Conductive
30838-060	3U	21HP	1	Screw-on Front	Anodized	Conductive
30847-466	5U	28HP	1	Screw-on Front	Anodized	Conductive
30847-461	2U	84HP	1	Screw-on Front	Anodized	Conductive

Catalog Number	Rack Height	Rack Width	Package Quantity	Mounting	Front Finish	Rear Finish
30838-049	3U	10HP	1	Screw-on Front	Anodized	Conductive
30847-482	9U	10HP	1	Screw-on Front	Anodized	Conductive
30838-124	6U	4HP	1	Screw-on Front	Anodized	Conductive

Table 1/3

Catalog Number	Treated Edges	Complies With	EMC Shielding	Height (H)	Width (W)	Certifications
30847-470	No	IEC 60297-3-101, IEEE 1101.1/10	No	128.4mm	9.8mm	RoHS
30847-464	No	IEC 60297-3-101, IEEE 1101.1/10	No	172.9mm	319.7mm	RoHS
30847-480	No	IEC 60297-3-101, IEEE 1101.1/10	No	395.1mm	40.3mm	RoHS
30838-125	No	IEC 60297-3-101, IEEE 1101.1/10	No	261.8mm	25mm	RoHS
30838-148	No	IEC 60297-3-101, IEEE 1101.1/10	No	261.8mm	141.9mm	RoHS
30838-183	No	IEC 60297-3-101, IEEE 1101.1/10	No	261.8mm	319.7mm	RoHS
30838-047	No	IEC 60297-3-101, IEEE 1101.1/10	No	128.4mm	40.3mm	RoHS
30838-067	No	IEC 60297-3-101, IEEE 1101.1/10	No	128.4mm	141.9mm	RoHS
30847-476	No	IEC 60297-3-101, IEEE 1101.1/10	No	395.1mm	20mm	RoHS
30838-127	No	IEC 60297-3-101, IEEE 1101.1/10	No	261.8mm	35.2mm	RoHS
30847-468	No	IEC 60297-3-101, IEEE 1101.1/10	No	217.4mm	319.7mm	
30847-463	No	IEC 60297-3-101, IEEE 1101.1/10	No	172.9mm	213mm	RoHS
30847-471	No	IEC 60297-3-101, IEEE 1101.1/10	No	128.4mm	14.9mm	RoHS
30838-046	No	IEC 60297-3-101, IEEE 1101.1/10	No	128.4mm	35.2mm	RoHS
30838-128	No	IEC 60297-3-101, IEEE 1101.1/10	No	261.8mm	40.3mm	RoHS
30838-126	No	IEC 60297-3-101, IEEE 1101.1/10	No	261.8mm	30.1mm	RoHS
30838-045	No	IEC 60297-3-101, IEEE 1101.1/10	No	128.4mm	30.1mm	RoHS

Catalog Number	TreatedEdges	Complies With	EMCShielding	Height(H)	Width(W)	Certifications
30838-130	No	IEC 60297-3-101, IEEE 1101.1/10	No	261.8mm	50.5mm	RoHS
30847-469	No	IEC 60297-3-101, IEEE 1101.1/10	No	217.4mm	426.4mm	
30838-081	No	IEC 60297-3-101, IEEE 1101.1/10	No	128.4mm	213mm	RoHS

Table 2/3

Catalog Number	Treated Edges	Complies With	EMC Shielding	Height (H)	Width (W)	Certifications
30838-123	No	IEC 60297-3-101, IEEE 1101.1/10	No	128.4mm	426.4mm	RoHS
30847-460	No	IEC 60297-3-101, IEEE 1101.1/10	No	84mm	319.7mm	
30838-141	No	IEC 60297-3-101, IEEE 1101.1/10	No	261.8mm	106.3mm	RoHS
30847-462	No	IEC 60297-3-101, IEEE 1101.1/10	No	172.9mm	141.9mm	
30838-132	No	IEC 60297-3-101, IEEE 1101.1/10	No	261.8mm	60.6mm	RoHS
30838-044	No	IEC 60297-3-101, IEEE 1101.1/10	No	128.4mm	25mm	RoHS
30838-043	No	IEC 60297-3-101, IEEE 1101.1/10	No	128.4mm	20mm	RoHS
30838-136	No	IEC 60297-3-101, IEEE 1101.1/10	No	261.8mm	80.9mm	RoHS
30838-134	No	IEC 60297-3-101, IEEE 1101.1/10	No	261.8mm	70.8mm	RoHS
30838-102	No	IEC 60297-3-101, IEEE 1101.1/10	No	128.4mm	319.7mm	RoHS
30847-467	No	IEC 60297-3-101, IEEE 1101.1/10	No	217.4mm	213mm	
30838-053	No	IEC 60297-3-101, IEEE 1101.1/10	No	128.4mm	70.8mm	RoHS
30847-459	No	IEC 60297-3-101, IEEE 1101.1/10	No	84mm	213mm	
30847-556	No	IEC 60297-3-101, IEEE 1101.1/10	No	395.1mm	426.4mm	RoHS
30847-458	No	IEC 60297-3-101, IEEE 1101.1/10	No	84mm	141.9mm	



Catalog Number	TreatedEdges	Complies With	EMCShielding	Height(H)	Width(W)	Certification s
30838-055	No	IEC 60297-3-101, IEEE 1101.1/10	No	128.4mm	80.9mm	RoHS
30838-162	No	IEC 60297-3-101, IEEE 1101.1/10	No	261.8mm	213mm	RoHS
30838-204	No	IEC 60297-3-101, IEEE 1101.1/10	No	261.8mm	426.4mm	RoHS
30847-484	No	IEC 60297-3-101, IEEE 1101.1/10	No	395.1mm	60.6mm	RoHS
30847-465	No	IEC 60297-3-101, IEEE 1101.1/10	No	172.9mm	426.4mm	RoHS

Table 3/3

Catalog Number	Treated Edges	Complies With	EMC Shielding	Height (H)	Width (W)	Certification s
30838-051	No	IEC 60297-3-101, IEEE 1101.1/10	No	128.4mm	60.6mm	RoHS
30838-060	No	IEC 60297-3-101, IEEE 1101.1/10	No	128.4mm	106.3mm	RoHS
30847-466	No	IEC 60297-3-101, IEEE 1101.1/10	No	217.4mm	141.9mm	
30847-461	No	IEC 60297-3-101, IEEE 1101.1/10	No	84mm	426.4mm	RoHS
30838-049	No	IEC 60297-3-101, IEEE 1101.1/10	No	128.4mm	50.5mm	RoHS
30847-482	No	IEC 60297-3-101, IEEE 1101.1/10	No	395.1mm	50.5mm	RoHS
30838-124	No	IEC 60297-3-101, IEEE 1101.1/10	No	261.8mm	20mm	RoHS

ADDITIONAL PRODUCT DETAILS

Please order fixing material (sleeves, collar screws) separately.



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE