

# nVent CADDY Speed Link SLK with Threaded Stud End



## FEATURES

Complete system includes wire, locking device and pre-assembled threaded stud end fitting

Attaches to structures with threaded anchors or devices with threaded hole

Connects directly to threaded devices in trapeze assemblies, light fixtures, HVAC assemblies or signage

**Material:** Steel;Polypropylene;Zinc Alloy  
**Finish:** Electrogalvanized  
**Static Load Safety Factor:** 5:1  
**Complies With:** SMACNA HVAC-DCS



## SPECIFICATIONS

Table 1/2


| Catalog Number | Article Number | Wire Rope Diameter | Wire Rope Length | Rod Size (RS) | Screw Length (L) | Height (H) |
|----------------|----------------|--------------------|------------------|---------------|------------------|------------|
| SLK15L1SEM6    | 196564         | 1.5 mm             | 1m               | 6             | 25mm             | 55 mm      |
| SLK15L1SEM8    | 196565         | 1.5 mm             | 1m               | 8             | 45mm             | 55 mm      |
| SLK15L2SEM6    | 196566         | 1.5 mm             | 2m               | 6             | 25mm             | 55 mm      |
| SLK15L2SEM8    | 196567         | 1.5 mm             | 2m               | 8             | 45mm             | 55 mm      |
| SLK15L3SEM6    | 196568         | 1.5 mm             | 3m               | 6             | 25mm             | 55 mm      |
| SLK15L3SEM8    | 196570         | 1.5 mm             | 3m               | 8             | 45mm             | 55 mm      |
| SLK2L2SEM8     | 196559         | 2 mm               | 2m               | 8             | 45mm             | 55 mm      |
| SLK2L3SEM8     | 196561         | 2 mm               | 3m               | 8             | 45mm             | 55 mm      |
| SLK2L5SEM6     | 196562         | 2 mm               | 5m               | 6             | 25mm             | 55 mm      |

| Catalog Number | ArticleNumber | Wire RopeDiameter | Wire RopeLength | Rod Size(RS) | Screw Length(L) | Height(H) |
|----------------|---------------|-------------------|-----------------|--------------|-----------------|-----------|
| SLK2L5SEM8     | 196563        | 2 mm              | 5m              | 8            | 45mm            | 55 mm     |

Table 2/2

| Catalog Number | Article Number | Width (W) | Thickness (T) | Angle (a) | Static Load |
|----------------|----------------|-----------|---------------|-----------|-------------|
| SLK15L1SEM6    | 196564         | 19 mm     | 12.5 mm       | 90 ° Max  | 195N        |
| SLK15L1SEM8    | 196565         | 19 mm     | 12.5 mm       | 90 ° Max  | 195N        |
| SLK15L2SEM6    | 196566         | 19 mm     | 12.5 mm       | 90 ° Max  | 195N        |
| SLK15L2SEM8    | 196567         | 19 mm     | 12.5 mm       | 90 ° Max  | 195N        |
| SLK15L3SEM6    | 196568         | 19 mm     | 12.5 mm       | 90 ° Max  | 195N        |
| SLK15L3SEM8    | 196570         | 19 mm     | 12.5 mm       | 90 ° Max  | 195N        |
| SLK2L2SEM8     | 196559         | 19 mm     | 12.5 mm       | 90 ° Max  | 440N        |
| SLK2L3SEM8     | 196561         | 19 mm     | 12.5 mm       | 90 ° Max  | 440N        |
| SLK2L5SEM6     | 196562         | 19 mm     | 12.5 mm       | 90 ° Max  | 440N        |
| SLK2L5SEM8     | 196563         | 19 mm     | 12.5 mm       | 90 ° Max  | 440N        |

## DIAGRAMS



## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

#### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

#### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

#### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

#### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

