


2000 Beam Clamp Kit

FEATURES

Light duty system

Includes clamp and U channel



Material: Steel
Finish: Electrogalvanized

SPECIFICATIONS

Table 1/2

Catalog Number	Article Number	Length (L)	A	B	C	D
2200EG	570140	200mm	25 mm	25 mm	65 mm	25 mm
2300EG	570160	300mm	25 mm	25 mm	65 mm	25 mm
2350EG	570170	350mm	25 mm	25 mm	65 mm	25 mm
2400EG	570180	400mm	25 mm	25 mm	65 mm	25 mm
2250EG	570150	250mm	25 mm	25 mm	65 mm	25 mm

Table 2/2


Catalog Number	Article Number	E	Static Load 1 (F1)	Static Load 2 (F2)	Static Load 3 (F3)
2200EG	570140	30.5 mm	1700N	490N	340N
2300EG	570160	30.5 mm	1700N	490N	340N
2350EG	570170	55.5 mm	1700N	490N	340N
2400EG	570180	30.5 mm	1700N	490N	340N
2250EG	570150	55.5 mm	1700N	490N	340N

Height (H):	12 mm
Width (W):	25 mm
Thickness (T):	2 mm
Flange Thickness (FT):	11 mm Max
Hole Size (HS):	11 mm
Screw Diameter (Sc):	6
Torque (TQ):	30 N·m

ADDITIONAL PRODUCT DETAILS

For a secure grip the channel must extend to the outer edge of each beam clamp.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

