


# nVent CADDY Pyramid Equipment Support Post Base



## FEATURES

Ideal for use with strut channel type A and U-shaped brackets to create custom equipment supports

Height adjustable

Foam bottom offers low abrasion interface for better roof membrane protection

Compatible with roof surfaces including single ply, bituminous, metal and spray foam

Provides superior load distribution, even with varying rooftop surfaces

Hot-dip galvanized and UV stabilized for long lasting performance

## SPECIFICATIONS

Table 1/3

| Catalog Number | Article Number | E-Number | Material                           | Finish             | Temperature    | Static Load Safety Factor |
|----------------|----------------|----------|------------------------------------|--------------------|----------------|---------------------------|
| PEB            | 360425         | 1653294  | Steel, Polypropylene, Polyethylene | Hot-Dip Galvanized | -34 to 54.4 °C | 3:1                       |

Table 2/3

| Catalog Number | Article Number | E-Number | Height (H)   | Length (L) | Width (W) | A     |
|----------------|----------------|----------|--------------|------------|-----------|-------|
| PEB            | 360425         | 1653294  | 305 - 457 mm | 314mm      | 314 mm    | 76 mm |

Table 3/3

| Catalog Number | Article Number | E-Number | Surface Area       | Unit Weight | Static Load |
|----------------|----------------|----------|--------------------|-------------|-------------|
| PEB            | 360425         | 1653294  | 0.09m <sup>2</sup> | 4 kg        | 3340N       |

## ADDITIONAL PRODUCT DETAILS

The end user must select and evaluate the strut framing to ensure the custom assembled equipment support can properly support the applied load.



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

Europe

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

Europe

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

APAC

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500

