

300 Universal Beam Clamp



FEATURES

Conforms with Federal Specification WW-H-171 (Type 23), Manufacturers Standardization Society (MSS) SP-58 (Type 19 and 23)

Material: Cast Iron



SPECIFICATIONS

Table 1/2

Catalog Number	Finish	Rod Size (RS)	Rod Size (RS)	Flange Thickness (FT)	A	Torque (TQ)
3000037EG	Electrogalvanized	3/8"	3/8"	3/4" Max	1 1/8"	5 ft·lbf
3000037PL	Plain	3/8"	3/8"	3/4" Max	1 1/8"	5 ft·lbf
3000050EG	Electrogalvanized	1/2"	1/2"	3/4" Max	1 1/8"	8 ft·lbf
3000050PL	Plain	1/2"	1/2"	3/4" Max	1 1/8"	8 ft·lbf
3000062EG	Electrogalvanized	5/8"	5/8"	3/4" Max	1 1/8"	5 ft·lbf
3000062PL	Plain	5/8"	5/8"	3/4" Max	1 1/8"	5 ft·lbf
3000075EG	Electrogalvanized	3/4"	3/4"	3/4" Max	1 1/8"	5 ft·lbf
3000075PL	Plain	3/4"	3/4"	3/4" Max	1 1/8"	5 ft·lbf
3000087EG	Electrogalvanized	7/8"	7/8"	3/4" Max	1 1/8"	5 ft·lbf
3000087PL	Plain	7/8"	7/8"	3/4" Max	1 1/8"	5 ft·lbf


Table 2/2

Catalog Number	Static Load 1 (F1)	Static Load 2 (F2)	Certifications
3000037EG	500lb	250lb	cUL, UL, FM Approved, Pipe Hanger Components
3000037PL	500lb	250lb	FM Approved, Pipe Hanger Components, UL, cUL
3000050EG	950lb	760lb	UL, FM Approved, Pipe Hanger Components, cUL
3000050PL	950lb	760lb	UL, cUL, FM Approved, Pipe Hanger Components
3000062EG	950lb	760lb	UL, cUL
3000062PL	950lb	760lb	UL, cUL
3000075EG	950lb	760lb	UL, cUL
3000075PL	950lb	760lb	UL, cUL
3000087EG	950lb	760lb	UL, cUL
3000087PL	950lb	760lb	UL, cUL

ADDITIONAL PRODUCT DETAILS

Setscrew must be tightened and torqued onto the sloped side of the I-beam.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

