

Bolt Close Conduit/Pipe Clamp



FEATURES

Retained bolt and built-in nut means there are less parts to handle or drop

Combo head bolt works with slotted, hex, #3 phillips or #2 robertson drivers



SPECIFICATIONS

Table 1/2

Catalog Number	Material	Finish	Nut Type	Outer Diameter (OD)	EMT Conduit Size	Rigid Conduit/Pipe Size
CD0B	Steel	Electrogalvanized	Built-In Nut	0.670" - 0.84"	1/2"	1/2"
CD0B37 	Steel	Electrogalvanized	Built-In Nut	0.670" - 0.84"	1/2"	1/2"
CD0BSS	Stainless Steel 304 (EN 1.4301)		Hex Nut	0.670" - 0.84"	1/2"	1/2"
CD1B 	Steel	Electrogalvanized	Built-In Nut	0.740" - 1.05"	3/4"	3/4"
CD1B37 	Steel	Electrogalvanized	Built-In Nut	0.740" - 1.05"	3/4"	3/4"
CD1BSS	Stainless Steel 304 (EN 1.4301)		Hex Nut	0.740" - 1.05"	3/4"	3/4"

Catalog Number	Material	Finish	Nut Type	Outer Diameter (OD)	EMT Conduit Size	Rigid Conduit/PipeSize
CD2.5B	Steel	Electrogalvanized	Built-In Nut	1.220" - 1.51"	1 1/4"	
CD2.5B37	Steel	Electrogalvanized	Built-In Nut	1.220" - 1.51"	1 1/4"	
CD2.5BSS	Stainless Steel 304 (EN 1.4301)		Hex Nut	1.220" - 1.51"	1 1/4"	
CD2B	Steel	Electrogalvanized	Built-In Nut	1.000" - 1.31"	1"	1"
CD2B37	Steel	Electrogalvanized	Built-In Nut	1.000" - 1.31"	1"	1"
CD2BSS	Stainless Steel 304 (EN 1.4301)		Hex Nut	1.000" - 1.31"	1"	1"
CD3B	Steel	Electrogalvanized	Built-In Nut	1.410" - 1.74"	1 1/2"	1 1/4"
CD3B37	Steel	Electrogalvanized	Built-In Nut	1.410" - 1.74"	1 1/2"	1 1/4"
CD3BSS	Stainless Steel 304 (EN 1.4301)		Hex Nut	1.410" - 1.74"	1 1/2"	1 1/4"
CD4B	Steel	Electrogalvanized	Built-In Nut	1 3/4" - 1.9"		1 1/2"
CD4B37	Steel	Electrogalvanized	Built-In Nut	1 3/4" - 1.9"		1 1/2"
CD4BSS	Stainless Steel 304 (EN 1.4301)		Hex Nut	1 3/4" - 1.9"		1 1/2"
CD5B	Steel	Electrogalvanized	Built-In Nut	1.910" - 2.88"	2"	2"
CD5B37	Steel	Electrogalvanized	Built-In Nut	1.910" - 2.88"	2"	2"

Table 2/2

Catalog Number	Material	Finish	Nut Type	Outer Diameter (OD)	EMT Conduit Size	Rigid Conduit/Pipe Size
CD5BSS	Stainless Steel 304 (EN 1.4301)		Hex Nut	1.910" - 2.88"	2"	2"
CD6B	Steel	Electrogalvanized	Hex Nut	2.6" - 3"	2 1/2"	2 1/2"
CD6BSS	Stainless Steel 304 (EN 1.4301)		Hex Nut	2.6" - 3"	2 1/2"	2 1/2"
CD7B	Steel	Electrogalvanized	Hex Nut	3.150" - 3 1/2"	3"	3"

Catalog Number	Material	Finish	Nut Type	Outer Diameter (OD)	EMT Conduit Size	Rigid Conduit/Pipe Size
CD7BSS	Stainless Steel 304 (EN 1.4301)		Hex Nut	3.150" - 3 1/2"	3"	3"
CD8B	Steel	Electrogalvanized	Hex Nut	3.740" - 4.13"	3 1/2"	3 1/2"
CD8BSS	Stainless Steel 304 (EN 1.4301)		Hex Nut	3.740" - 4.13"	3 1/2"	3 1/2"
CD9B	Steel	Electrogalvanized	Hex Nut	4 1/4" - 4.53"	4"	4"
CD9BSS	Stainless Steel 304 (EN 1.4301)		Hex Nut	4 1/4" - 4.53"	4"	4"

Table 1/2

Catalog Number	Hole Size (HS)	Static Load 1 (F1)	Static Load 2 (F2)	Certifications
CD0B	0.28"	200lb	50lb	cUL, UL
CD0B37 	0.41"	200lb	50lb	
CD0BSS	0.28"	200lb	50lb	cUL, UL
CD1B 	0.28"	200lb	50lb	cUL, UL, ITB
CD1B37 	0.41"	200lb	50lb	
CD1BSS	0.28"	200lb	50lb	UL, cUL
CD2.5B	0.28"	200lb	50lb	UL, cUL
CD2.5B37	0.41"	200lb	50lb	
CD2.5BSS	0.27"	200lb	50lb	UL, cUL
CD2B	0.28"	200lb	50lb	UL, cUL
CD2B37	0.41"	200lb	50lb	
CD2BSS	0.27"	200lb	50lb	
CD3B	0.28"	200lb	50lb	UL, cUL, ITB
CD3B37	0.41"	200lb	50lb	
CD3BSS	0.27"	200lb	50lb	UL, cUL
CD4B	0.28"	200lb	50lb	cUL, ITB, UL
CD4B37	0.41"	200lb	50lb	
CD4BSS	0.28"	200lb	50lb	cUL, UL
CD5B	0.28"	200lb	50lb	UL, cUL, ITB
CD5B37	0.41"	200lb	50lb	

Table 2/2

Catalog Number	Hole Size (HS)	Static Load 1 (F1)	Static Load 2 (F2)	Certifications
CD5BSS	0.28"	350lb	50lb	UL, cUL

Catalog Number	Hole Size (HS)	Static Load 1 (F1)	Static Load 2 (F2)	Certifications
CD6B	5/16"	350lb	50lb	
CD6BSS	0.33"	350lb	50lb	
CD7B	5/16"	350lb	50lb	
CD7BSS	0.33"	350lb	50lb	
CD8B	5/16"	350lb	50lb	
CD8BSS	0.33"	350lb	50lb	
CD9B	5/16"	350lb	50lb	
CD9BSS	0.33"	350lb	50lb	

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

