

Wire Basket Tray Shaped Wire 2"X4"X118", Pewter, Pregalvanized

CATALOG NUMBER

WBT2X4SPW

The construction of the nVent CADDY Wire Basket Tray, Shaped Wire eliminates stress and pressure points on today's high-speed/performance cabling media. The backbone of the platform features our "Shaped Tray" technology—offering substantial support improvement over traditional wire mesh tray. This technology increases support by 400% while reducing cable strain up to 65%, protecting high-performance and fiber optic cable for the life of the installation.

FEATURES

Provides optimal support for high-performance data cable, up to and including fiber optic, Cat 5e, Cat 6, Cat 6A, and Cat 7

UL Classified as an equipment ground conductor, no field removal of paint required

T-Weld edge wire for cable and installer protection

Mill Certificates are available to document recycled content for possible LEED credits/certification



PRODUCT ATTRIBUTES

Material: Steel

Finish: Pregalvanized; Powder Coated

Color: Pewter

Height (H): 2



Width (W): 4

Length (L): 118"

Unit Weight: 8 lb

6" DEEP TRAY	
Tray Size	Splice Qty
6X8	3
6X12	3
6X16	3
6X18	4
6X20	4
6X22	4
6X24	4
6X26	5
6X28	5
6X30	5
6X32	6
6X34	6
6X36	7
These products are also available for Shaped Cable Tray and can be found by including an S to the end of any part number above	

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

