

nVent CADDY Pyramid H-Frame Post Base



FEATURES

Foam or rubber bottom offers low abrasion interface for better roof membrane protection

Compatible with roof surfaces including single ply, bituminous, metal and spray foam

Provides superior load distribution, even with varying rooftop surfaces

Rubber rooftop interface ideal for solar panel array installations

Mounting hardware pre-installed in bases

Hot-dip galvanized and UV stabilized for long lasting performance

Accepts standard strut channels

Material:	Steel;Polypropylene;Polyethylene
Finish:	Hot-Dip Galvanized
Temperature:	-30 to 130 °F
Static Load Safety Factor:	3:1


SPECIFICATIONS

Table 1/2

Catalog Number	Rooftop Interface	Strut Type	Height (H)	Length (L)	Width (W)	Surface Area
PHB	Foam	A (1 5/8" x 1 5/8")	4.6"	12 3/8"	12 3/8"	144in ²
PHBR	Rubber	A (1 5/8" x 1 5/8")	4.66"	12 3/8"	12 3/8"	144in ²

Table 2/2

Catalog Number	Unit Weight	Static Load (F)
PHB	3.9 lb	750lbf
PHBR	4.5 lb	750lbf



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

