

nVent CADDY Speed Link SLS with Decking Hook



FEATURES

Complete system includes wire, locking device and pre-assembled decking hook end fitting

Quickly and easily attaches to hollow metal decking

Spring-loaded ends snap into decking hole and lock into place

Innovative design helps protect the wire from sharp edges of decking hole, minimizing risk of damage to wire

Finger tightening of nut secures the locking device into position without tools

Installs in strut profiles without the need to insert fingers or tools into the strut



SPECIFICATIONS

Table 1/2

Catalog Number	Material	Finish	Static Load Safety Factor	Complies With	Wire Rope Diameter	Wire Rope Length
SLS2L3DH	Steel, Zinc Alloy, Polypropylene	Electrogalvanized	5:1	SMACNA HVAC-DCS	2 mm	9.9'

Table 2/2

Catalog Number	Roof Decking Sheet Thickness	A	Hole Size 1 (HS1)	Static Load (F)
SLS2L3DH	16 ga Max	0.36"	0.32"	60lb

Thread Size (TS):	M8
Height 1 (H1):	2.1"
Height 2 (H2):	1.8"
Width (W):	0.6"
Thickness (T):	0.15" Max
Hole Size 2 (HS2):	0.310" - 0.38"

Slot Size (SS): 0.31" x 0.25" - 0.31" x 0.38"

ADDITIONAL PRODUCT DETAILS


The 2 mm locking device is compatible with C-Channel Types E0 and E0L.

Total load per wire on a multi-tier trapeze must not exceed static load.

Load rating is only applicable if the load-bearing capacity of the supporting element (steel decking) is adequate.

Check with deck manufacturer for recommended load capacity.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

