

nVent CADDY Superklip



FEATURES

Closes and locks automatically when the pipe, tube or cable is inserted

One-piece clamp for fast and convenient installation

Fasten with either wood screw, dual threaded screw with or without collar, nail with collar, threaded rod, mounting plate or shot-fire bracket

Material: Xenoy®
Temperature: -13 to 194 °F

SPECIFICATIONS

Catalog Number	Outer Diameter (OD)	Rigid Conduit Size	Pipe Size	Copper Tube Size	B	C	Static Load (F)
389001	0.460" - 0.56"			3/8"	9/16"	1 3/16"	35lbf
389002	0.560" - 0.66"			1/2"	9/16"	1 3/16"	40lbf
389003	0.660" - 0.77"	3/8"	3/8"	5/8"	5/8"	1 13/32"	43lbf
389004	0.770" - 0.86"	1/2"	1/2"		5/8"	1 9/16"	50lbf
389005	0.860" - 0.98"			3/4"	21/32"	1 5/8"	48lbf
389006	0.980" - 1.09"	3/4"	3/4"		11/16"	1 3/4"	54lbf
389007	1.090" - 1.23"			1"	11/16"	1 15/16"	58lbf
389008	1.230" - 1.4"	1"	1"	1 1/4"	11/16"	2 1/8"	67lbf

Catalog Number	Outer Diameter (OD)	Rigid Conduit Size	Pipe Size	Copper Tube Size	B	C	Static Load (F)
389009	1.400" - 1.56"			1 1/4"	11/16"	2 5/16"	72lbf
389011	1.560" - 1.71"	1 1/4"	1 1/4" Min	1 1/2"	3/4"	2 1/2"	80lbf
389012	1.83" - 2"	1 1/2"	1 1/2"		3/4"	2 7/8"	84lbf
389013	2.000" - 2.19"			2"	25/32"	3 3/32"	90lbf
389014	2.300" - 2.52"	2"	2" Min		13/16"	3 15/32"	92lbf
389017	0.310" - 0.37"			1/4"	11/16"	11/16"	30lbf
389018	0.370" - 0.46"			1/4"	11/16"	11/16"	33lbf

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

