

Universal Restraint Clip



FEATURES

Attaches cable brace to structure

Meets CEN/TS 17551:2021 requirements for Seismic Sway Bracing

SPECIFICATIONS

Catalog Number	Material	Finish	Brace Size	Hole Size (HS)	Thickness (T)	UL Listed Load	Certifications
CSBURC12 	Steel	Electrogalvanized	#12, #18, #36	9/16"	0.17"	771lb	ICC-ES (Seismic Cable Bracing), ICC-ES, cUL, OSHPD/HCAI, UL
CSBURC12SS 	Stainless Steel 316 (EN 1.4401)		#12, #18, #36	9/16"	0.17"	618lb	
CSBURC38 	Steel	Electrogalvanized	#12, #18, #36	7/16"	0.17"	771lb	ICC-ES, ICC-ES (Seismic Cable Bracing), OSHPD/HCAI, UL, cUL
CSBURC38SS 	Stainless Steel 316 (EN 1.4401)		#12, #18, #36	7/16"	0.17"	618lb	
CSBURC58 	Steel	Electrogalvanized	#12, #18, #36	11/16"	0.17"	771lb	OSHPD/HCAI, UL, cUL, ICC-ES (Seismic Cable Bracing), ICC-ES
CSBURC58SS 	Stainless Steel 316 (EN 1.4401)		#12, #18, #36	11/16"	0.17"	618lb	


ADDITIONAL PRODUCT DETAILS

Brace member is not included.

Mount to the structure using the center hole. Loop cable through the holes in the bent tabs and swage in place.

UL Loads		
Part Number	Brace Member	Load Rating
CSBURC38	CSB12CBL	418 lb
	CSB18CBL	772 lb
	CSB36CBL	1909 lb
CSBURC12	CSB12CBL	418 lb
	CSB18CBL	772 lb
	CSB36CBL	1909 lb
CSBURC58	CSB12CBL	418 lb
	CSB18CBL	772 lb
	CSB36CBL	1909 lb

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

