


Low Impedance Riser



FEATURES

Used to connect the signal reference grid to equipment


Welded to the SRG using nVent ERICO Cadweld mold type TW

Has a lower impedance than a 4/0 AWG copper conductor

Material: Copper

SPECIFICATIONS

Catalog Number	Length (L)	Width (W)	Thickness (T)	Hole Size (HS)
B802D01A24	24"	2"	26ga	5/16"
B802D01A5	5"	2"	26ga	5/16"
B802D01A36	36"	2"	26ga	5/16"
B802D01A120 	120"	2"	26ga	5/16"
B802D01A12	12"	2"	26ga	5/16"
B802D01A48	48"	2"	26ga	5/16"



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE