

# nVent ERICO Ericore Terminated Conductor



## FEATURES

Low-inductance, low-impedance cable designed to minimize voltage build-up due to lightning impulses

Multiple insulated layers of conductor reduce the potential of side flashing

Upper termination provides an insulated connection from terminal to nVent ERICO Ericore to properly transition the lightning strike

Requires lower termination kit

## SPECIFICATIONS

Table 1/6

| Catalog Number | Capacitance | Diameter (Ø) | Impedance | Inductance | Resistance (Rdc) | Resistance (Rimp) |
|----------------|-------------|--------------|-----------|------------|------------------|-------------------|
| ERICORE054T    | 0.75 nF     | 1.42"        | 12 Ω Max  | 37nH       | 0.5mΩ·m          | 6mΩ·m             |
| ERICORE049T    | 0.75 nF     | 1.42"        | 12 Ω Max  | 37nH       | 0.5mΩ·m          | 6mΩ·m             |
| ERICORE097T    | 0.75 nF     | 1.42"        | 12 Ω Max  | 37nH       | 0.5mΩ·m          | 6mΩ·m             |
| ERICORE050T    | 0.75 nF     | 1.42"        | 12 Ω Max  | 37nH       | 0.5mΩ·m          | 6mΩ·m             |
| ERICORE010T    | 0.75 nF     | 1.42"        | 12 Ω Max  | 37nH       | 0.5mΩ·m          | 6mΩ·m             |
| ERICORE107T    | 0.75 nF     | 1.42"        | 12 Ω Max  | 37nH       | 0.5mΩ·m          | 6mΩ·m             |
| ERICORE033T    | 0.75 nF     | 1.42"        | 12 Ω Max  | 37nH       | 0.5mΩ·m          | 6mΩ·m             |
| ERICORE051T    | 0.75 nF     | 1.42"        | 12 Ω Max  | 37nH       | 0.5mΩ·m          | 6mΩ·m             |
| ERICORE095T    | 0.75 nF     | 1.42"        | 12 Ω Max  | 37nH       | 0.5mΩ·m          | 6mΩ·m             |
| ERICORE052T    | 0.75 nF     | 1.42"        | 12 Ω Max  | 37nH       | 0.5mΩ·m          | 6mΩ·m             |
| ERICORE032T    | 0.75 nF     | 1.42"        | 12 Ω Max  | 37nH       | 0.5mΩ·m          | 6mΩ·m             |
| ERICORE155T    | 0.75 nF     | 1.42"        | 12 Ω Max  | 37nH       | 0.5mΩ·m          | 6mΩ·m             |
| ERICORE053T    | 0.75 nF     | 1.42"        | 12 Ω Max  | 37nH       | 0.5mΩ·m          | 6mΩ·m             |
| ERICORE009T    | 0.75 nF     | 1.42"        | 12 Ω Max  | 37nH       | 0.5mΩ·m          | 6mΩ·m             |

| Catalog Number | Capacitance | Diameter (Ø) | Impedance | Inductance | Resistance (Rdc) | Resistance (Rimp) |
|----------------|-------------|--------------|-----------|------------|------------------|-------------------|
| ERICORE092T    | 0.75 nF     | 1.42"        | 12 Ω Max  | 37nH       | 0.5mΩ·m          | 6mΩ·m             |
| ERICORE034T    | 0.75 nF     | 1.42"        | 12 Ω Max  | 37nH       | 0.5mΩ·m          | 6mΩ·m             |
| ERICORE016T    | 0.75 nF     | 1.42"        | 12 Ω Max  | 37nH       | 0.5mΩ·m          | 6mΩ·m             |
| ERICORE110T    | 0.75 nF     | 1.42"        | 12 Ω Max  | 37nH       | 0.5mΩ·m          | 6mΩ·m             |
| ERICORE031T    | 0.75 nF     | 1.42"        | 12 Ω Max  | 37nH       | 0.5mΩ·m          | 6mΩ·m             |
| ERICORE055T    | 0.75 nF     | 1.42"        | 12 Ω Max  | 37nH       | 0.5mΩ·m          | 6mΩ·m             |

Table 2/6

| Catalog Number | Capacitance | Diameter (Ø) | Impedance | Inductance | Resistance (Rdc) | Resistance (Rimp) |
|----------------|-------------|--------------|-----------|------------|------------------|-------------------|
| ERICORE091T    | 0.75 nF     | 1.42"        | 12 Ω Max  | 37nH       | 0.5mΩ·m          | 6mΩ·m             |
| ERICORE030T    | 0.75 nF     | 1.42"        | 12 Ω Max  | 37nH       | 0.5mΩ·m          | 6mΩ·m             |
| ERICORE008T    | 0.75 nF     | 1.42"        | 12 Ω Max  | 37nH       | 0.5mΩ·m          | 6mΩ·m             |
| ERICORE056T    | 0.75 nF     | 1.42"        | 12 Ω Max  | 37nH       | 0.5mΩ·m          | 6mΩ·m             |
| ERICORE090T    | 0.75 nF     | 1.42"        | 12 Ω Max  | 37nH       | 0.5mΩ·m          | 6mΩ·m             |
| ERICORE112T    | 0.75 nF     | 1.42"        | 12 Ω Max  | 37nH       | 0.5mΩ·m          | 6mΩ·m             |
| ERICORE057T    | 0.75 nF     | 1.42"        | 12 Ω Max  | 37nH       | 0.5mΩ·m          | 6mΩ·m             |
| ERICORE029T    | 0.75 nF     | 1.42"        | 12 Ω Max  | 37nH       | 0.5mΩ·m          | 6mΩ·m             |
| ERICORE058T    | 0.75 nF     | 1.42"        | 12 Ω Max  | 37nH       | 0.5mΩ·m          | 6mΩ·m             |
| ERICORE088T    | 0.75 nF     | 1.42"        | 12 Ω Max  | 37nH       | 0.5mΩ·m          | 6mΩ·m             |
| ERICORE012T    | 0.75 nF     | 1.42"        | 12 Ω Max  | 37nH       | 0.5mΩ·m          | 6mΩ·m             |
| ERICORE039T    | 0.75 nF     | 1.42"        | 12 Ω Max  | 37nH       | 0.5mΩ·m          | 6mΩ·m             |
| ERICORE104T    | 0.75 nF     | 1.42"        | 12 Ω Max  | 37nH       | 0.5mΩ·m          | 6mΩ·m             |
| ERICORE040T    | 0.75 nF     | 1.42"        | 12 Ω Max  | 37nH       | 0.5mΩ·m          | 6mΩ·m             |
| ERICORE038T    | 0.75 nF     | 1.42"        | 12 Ω Max  | 37nH       | 0.5mΩ·m          | 6mΩ·m             |
| ERICORE013T    | 0.75 nF     | 1.42"        | 12 Ω Max  | 37nH       | 0.5mΩ·m          | 6mΩ·m             |
| ERICORE041T    | 0.75 nF     | 1.42"        | 12 Ω Max  | 37nH       | 0.5mΩ·m          | 6mΩ·m             |
| ERICORE102T    | 0.75 nF     | 1.42"        | 12 Ω Max  | 37nH       | 0.5mΩ·m          | 6mΩ·m             |
| ERICORE014T    | 0.75 nF     | 1.42"        | 12 Ω Max  | 37nH       | 0.5mΩ·m          | 6mΩ·m             |
| ERICORE042T    | 0.75 nF     | 1.42"        | 12 Ω Max  | 37nH       | 0.5mΩ·m          | 6mΩ·m             |

Table 3/6

| Catalog Number | Capacitance | Diameter (Ø) | Impedance | Inductance | Resistance (Rdc) | Resistance (Rimp) |
|----------------|-------------|--------------|-----------|------------|------------------|-------------------|
| ERICORE105T    | 0.75 nF     | 1.42"        | 12 Ω Max  | 37nH       | 0.5mΩ·m          | 6mΩ·m             |
| ERICORE037T    | 0.75 nF     | 1.42"        | 12 Ω Max  | 37nH       | 0.5mΩ·m          | 6mΩ·m             |
| ERICORE043T    | 0.75 nF     | 1.42"        | 12 Ω Max  | 37nH       | 0.5mΩ·m          | 6mΩ·m             |

| Catalog Number | Capacitance | Diameter (Ø) | Impedance | Inductance | Resistance (Rdc) | Resistance (Rimp) |
|----------------|-------------|--------------|-----------|------------|------------------|-------------------|
| ERICORE101T    | 0.75 nF     | 1.42"        | 12 Ω Max  | 37nH       | 0.5mΩ·m          | 6mΩ·m             |
| ERICORE150T    | 0.75 nF     | 1.42"        | 12 Ω Max  | 37nH       | 0.5mΩ·m          | 6mΩ·m             |
| ERICORE020T    | 0.75 nF     | 1.42"        | 12 Ω Max  | 37nH       | 0.5mΩ·m          | 6mΩ·m             |
| ERICORE044T    | 0.75 nF     | 1.42"        | 12 Ω Max  | 37nH       | 0.5mΩ·m          | 6mΩ·m             |
| ERICORE036T    | 0.75 nF     | 1.42"        | 12 Ω Max  | 37nH       | 0.5mΩ·m          | 6mΩ·m             |
| ERICORE045T    | 0.75 nF     | 1.42"        | 12 Ω Max  | 37nH       | 0.5mΩ·m          | 6mΩ·m             |
| ERICORE100T    | 0.75 nF     | 1.42"        | 12 Ω Max  | 37nH       | 0.5mΩ·m          | 6mΩ·m             |
| ERICORE046T    | 0.75 nF     | 1.42"        | 12 Ω Max  | 37nH       | 0.5mΩ·m          | 6mΩ·m             |
| ERICORE106T    | 0.75 nF     | 1.42"        | 12 Ω Max  | 37nH       | 0.5mΩ·m          | 6mΩ·m             |
| ERICORE035T    | 0.75 nF     | 1.42"        | 12 Ω Max  | 37nH       | 0.5mΩ·m          | 6mΩ·m             |
| ERICORE011T    | 0.75 nF     | 1.42"        | 12 Ω Max  | 37nH       | 0.5mΩ·m          | 6mΩ·m             |
| ERICORE047T    | 0.75 nF     | 1.42"        | 12 Ω Max  | 37nH       | 0.5mΩ·m          | 6mΩ·m             |
| ERICORE098T    | 0.75 nF     | 1.42"        | 12 Ω Max  | 37nH       | 0.5mΩ·m          | 6mΩ·m             |
| ERICORE015T    | 0.75 nF     | 1.42"        | 12 Ω Max  | 37nH       | 0.5mΩ·m          | 6mΩ·m             |
| ERICORE048T    | 0.75 nF     | 1.42"        | 12 Ω Max  | 37nH       | 0.5mΩ·m          | 6mΩ·m             |
| ERICORE136T    | 0.75 nF     | 1.42"        | 12 Ω Max  | 37nH       | 0.5mΩ·m          | 6mΩ·m             |
| ERICORE003T    | 0.75 nF     | 1.42"        | 12 Ω Max  | 37nH       | 0.5mΩ·m          | 6mΩ·m             |

Table 4/6

| Catalog Number | Capacitance | Diameter (Ø) | Impedance | Inductance | Resistance (Rdc) | Resistance (Rimp) |
|----------------|-------------|--------------|-----------|------------|------------------|-------------------|
| ERICORE025T    | 0.75 nF     | 1.42"        | 12 Ω Max  | 37nH       | 0.5mΩ·m          | 6mΩ·m             |
| ERICORE083T    | 0.75 nF     | 1.42"        | 12 Ω Max  | 37nH       | 0.5mΩ·m          | 6mΩ·m             |
| ERICORE067T    | 0.75 nF     | 1.42"        | 12 Ω Max  | 37nH       | 0.5mΩ·m          | 6mΩ·m             |
| ERICORE120T    | 0.75 nF     | 1.42"        | 12 Ω Max  | 37nH       | 0.5mΩ·m          | 6mΩ·m             |
| ERICORE018T    | 0.75 nF     | 1.42"        | 12 Ω Max  | 37nH       | 0.5mΩ·m          | 6mΩ·m             |
| ERICORE005T    | 0.75 nF     | 1.42"        | 12 Ω Max  | 37nH       | 0.5mΩ·m          | 6mΩ·m             |
| ERICORE082T    | 0.75 nF     | 1.42"        | 12 Ω Max  | 37nH       | 0.5mΩ·m          | 6mΩ·m             |
| ERICORE024T    | 0.75 nF     | 1.42"        | 12 Ω Max  | 37nH       | 0.5mΩ·m          | 6mΩ·m             |
| ERICORE068T    | 0.75 nF     | 1.42"        | 12 Ω Max  | 37nH       | 0.5mΩ·m          | 6mΩ·m             |
| ERICORE125T    | 0.75 nF     | 1.42"        | 12 Ω Max  | 37nH       | 0.5mΩ·m          | 6mΩ·m             |
| ERICORE081T    | 0.75 nF     | 1.42"        | 12 Ω Max  | 37nH       | 0.5mΩ·m          | 6mΩ·m             |
| ERICORE069T    | 0.75 nF     | 1.42"        | 12 Ω Max  | 37nH       | 0.5mΩ·m          | 6mΩ·m             |
| ERICORE023T    | 0.75 nF     | 1.42"        | 12 Ω Max  | 37nH       | 0.5mΩ·m          | 6mΩ·m             |
| ERICORE080T    | 0.75 nF     | 1.42"        | 12 Ω Max  | 37nH       | 0.5mΩ·m          | 6mΩ·m             |
| ERICORE007T    | 0.75 nF     | 1.42"        | 12 Ω Max  | 37nH       | 0.5mΩ·m          | 6mΩ·m             |

| Catalog Number | Capacitance | Diameter (Ø) | Impedance | Inductance | Resistance (Rdc) | Resistance (Rimp) |
|----------------|-------------|--------------|-----------|------------|------------------|-------------------|
| ERICORE070T    | 0.75 nF     | 1.42"        | 12 Ω Max  | 37nH       | 0.5mΩ·m          | 6mΩ·m             |
| ERICORE078T    | 0.75 nF     | 1.42"        | 12 Ω Max  | 37nH       | 0.5mΩ·m          | 6mΩ·m             |
| ERICORE022T    | 0.75 nF     | 1.42"        | 12 Ω Max  | 37nH       | 0.5mΩ·m          | 6mΩ·m             |
| ERICORE071T    | 0.75 nF     | 1.42"        | 12 Ω Max  | 37nH       | 0.5mΩ·m          | 6mΩ·m             |
| ERICORE122T    | 0.75 nF     | 1.42"        | 12 Ω Max  | 37nH       | 0.5mΩ·m          | 6mΩ·m             |

Table 5/6

| Catalog Number | Capacitance | Diameter (Ø) | Impedance | Inductance | Resistance (Rdc) | Resistance (Rimp) |
|----------------|-------------|--------------|-----------|------------|------------------|-------------------|
| ERICORE077T    | 0.75 nF     | 1.42"        | 12 Ω Max  | 37nH       | 0.5mΩ·m          | 6mΩ·m             |
| ERICORE021T    | 0.75 nF     | 1.42"        | 12 Ω Max  | 37nH       | 0.5mΩ·m          | 6mΩ·m             |
| ERICORE200T    | 0.75 nF     | 1.42"        | 12 Ω Max  | 37nH       | 0.5mΩ·m          | 6mΩ·m             |
| ERICORE072T    | 0.75 nF     | 1.42"        | 12 Ω Max  | 37nH       | 0.5mΩ·m          | 6mΩ·m             |
| ERICORE001T    | 0.75 nF     | 1.42"        | 12 Ω Max  | 37nH       | 0.5mΩ·m          | 6mΩ·m             |
| ERICORE019T    | 0.75 nF     | 1.42"        | 12 Ω Max  | 37nH       | 0.5mΩ·m          | 6mΩ·m             |
| ERICORE076T    | 0.75 nF     | 1.42"        | 12 Ω Max  | 37nH       | 0.5mΩ·m          | 6mΩ·m             |
| ERICORE075T    | 0.75 nF     | 1.42"        | 12 Ω Max  | 37nH       | 0.5mΩ·m          | 6mΩ·m             |
| ERICORE006T    | 0.75 nF     | 1.42"        | 12 Ω Max  | 37nH       | 0.5mΩ·m          | 6mΩ·m             |
| ERICORE086T    | 0.75 nF     | 1.42"        | 12 Ω Max  | 37nH       | 0.5mΩ·m          | 6mΩ·m             |
| ERICORE028T    | 0.75 nF     | 1.42"        | 12 Ω Max  | 37nH       | 0.5mΩ·m          | 6mΩ·m             |
| ERICORE026T    | 0.75 nF     | 1.42"        | 12 Ω Max  | 37nH       | 0.5mΩ·m          | 6mΩ·m             |
| ERICORE087T    | 0.75 nF     | 1.42"        | 12 Ω Max  | 37nH       | 0.5mΩ·m          | 6mΩ·m             |
| ERICORE168T    | 0.75 nF     | 1.42"        | 12 Ω Max  | 37nH       | 0.5mΩ·m          | 6mΩ·m             |
| ERICORE017T    | 0.75 nF     | 1.42"        | 12 Ω Max  | 37nH       | 0.5mΩ·m          | 6mΩ·m             |
| ERICORE065T    | 0.75 nF     | 1.42"        | 12 Ω Max  | 37nH       | 0.5mΩ·m          | 6mΩ·m             |
| ERICORE060T    | 0.75 nF     | 1.42"        | 12 Ω Max  | 37nH       | 0.5mΩ·m          | 6mΩ·m             |
| ERICORE085T    | 0.75 nF     | 1.42"        | 12 Ω Max  | 37nH       | 0.5mΩ·m          | 6mΩ·m             |
| ERICORE064T    | 0.75 nF     | 1.42"        | 12 Ω Max  | 37nH       | 0.5mΩ·m          | 6mΩ·m             |
| ERICORE061T    | 0.75 nF     | 1.42"        | 12 Ω Max  | 37nH       | 0.5mΩ·m          | 6mΩ·m             |

Table 6/6

| Catalog Number | Capacitance | Diameter (Ø) | Impedance | Inductance | Resistance (Rdc) | Resistance (Rimp) |
|----------------|-------------|--------------|-----------|------------|------------------|-------------------|
| ERICORE066T    | 0.75 nF     | 1.42"        | 12 Ω Max  | 37nH       | 0.5mΩ·m          | 6mΩ·m             |
| ERICORE115T    | 0.75 nF     | 1.42"        | 12 Ω Max  | 37nH       | 0.5mΩ·m          | 6mΩ·m             |

Table 1/6

| Catalog Number | Upper Termination Voltage Withstand | Unit Weight |
|----------------|-------------------------------------|-------------|
| ERICORE054T    | 250kV                               | 144.24 lb   |

| Catalog Number | Upper Termination Voltage Withstand | Unit Weight |
|----------------|-------------------------------------|-------------|
| ERICORE049T    | 250kV                               | 131.24 lb   |
| ERICORE097T    | 250kV                               | 256.04 lb   |
| ERICORE050T    | 250kV                               | 133.84 lb   |
| ERICORE010T    | 250kV                               | 29.84 lb    |
| ERICORE107T    | 250kV                               | 282.04 lb   |
| ERICORE033T    | 250kV                               | 89.64 lb    |
| ERICORE051T    | 250kV                               | 136.44 lb   |
| ERICORE095T    | 250kV                               | 250.84 lb   |
| ERICORE052T    | 250kV                               | 139.03 lb   |
| ERICORE032T    | 250kV                               | 87.03 lb    |
| ERICORE155T    | 250kV                               | 406.83 lb   |
| ERICORE053T    | 250kV                               | 141.63 lb   |
| ERICORE009T    | 250kV                               | 27.23 lb    |
| ERICORE092T    | 250kV                               | 243.03 lb   |
| ERICORE034T    | 250kV                               | 92.23 lb    |
| ERICORE016T    | 250kV                               | 45.44 lb    |
| ERICORE110T    | 250kV                               | 289.83 lb   |
| ERICORE031T    | 250kV                               | 84.44 lb    |
| ERICORE055T    | 250kV                               | 146.84 lb   |

Table 2/6

| Catalog Number | Upper Termination Voltage Withstand | Unit Weight |
|----------------|-------------------------------------|-------------|
| ERICORE091T    | 250kV                               | 240.44 lb   |
| ERICORE030T    | 250kV                               | 81.83 lb    |
| ERICORE008T    | 250kV                               | 24.64 lb    |
| ERICORE056T    | 250kV                               | 149.44 lb   |
| ERICORE090T    | 250kV                               | 237.84 lb   |
| ERICORE112T    | 250kV                               | 295.04 lb   |
| ERICORE057T    | 250kV                               | 152.03 lb   |
| ERICORE029T    | 250kV                               | 79.23 lb    |
| ERICORE058T    | 250kV                               | 154.63 lb   |
| ERICORE088T    | 250kV                               | 232.63 lb   |
| ERICORE012T    | 250kV                               | 35.03 lb    |
| ERICORE039T    | 250kV                               | 105.23 lb   |
| ERICORE104T    | 250kV                               | 274.24 lb   |

| Catalog Number | Upper Termination Voltage Withstand | Unit Weight |
|----------------|-------------------------------------|-------------|
| ERICORE040T    | 250kV                               | 107.83 lb   |
| ERICORE038T    | 250kV                               | 102.64 lb   |
| ERICORE013T    | 250kV                               | 37.63 lb    |
| ERICORE041T    | 250kV                               | 110.44 lb   |
| ERICORE102T    | 250kV                               | 269.04 lb   |
| ERICORE014T    | 250kV                               | 40.23 lb    |
| ERICORE042T    | 250kV                               | 113.03 lb   |

Table 3/6

| Catalog Number | Upper Termination Voltage Withstand | Unit Weight |
|----------------|-------------------------------------|-------------|
| ERICORE105T    | 250kV                               | 276.83 lb   |
| ERICORE037T    | 250kV                               | 100.03 lb   |
| ERICORE043T    | 250kV                               | 115.64 lb   |
| ERICORE101T    | 250kV                               | 266.44 lb   |
| ERICORE150T    | 250kV                               | 393.83 lb   |
| ERICORE020T    | 250kV                               | 55.84 lb    |
| ERICORE044T    | 250kV                               | 118.23 lb   |
| ERICORE036T    | 250kV                               | 97.44 lb    |
| ERICORE045T    | 250kV                               | 120.83 lb   |
| ERICORE100T    | 250kV                               | 263.83 lb   |
| ERICORE046T    | 250kV                               | 123.44 lb   |
| ERICORE106T    | 250kV                               | 279.44 lb   |
| ERICORE035T    | 250kV                               | 94.83 lb    |
| ERICORE011T    | 250kV                               | 32.44 lb    |
| ERICORE047T    | 250kV                               | 126.03 lb   |
| ERICORE098T    | 250kV                               | 258.63 lb   |
| ERICORE015T    | 250kV                               | 42.84 lb    |
| ERICORE048T    | 250kV                               | 128.63 lb   |
| ERICORE136T    | 250kV                               | 357.44 lb   |
| ERICORE003T    | 250kV                               | 11.63 lb    |

Table 4/6

| Catalog Number | Upper Termination Voltage Withstand | Unit Weight |
|----------------|-------------------------------------|-------------|
| ERICORE025T    | 250kV                               | 68.83 lb    |
| ERICORE083T    | 250kV                               | 219.63 lb   |

| Catalog Number | Upper Termination Voltage Withstand | Unit Weight |
|----------------|-------------------------------------|-------------|
| ERICORE067T    | 250kV                               | 178.03 lb   |
| ERICORE120T    | 250kV                               | 315.83 lb   |
| ERICORE018T    | 250kV                               | 50.63 lb    |
| ERICORE005T    | 250kV                               | 16.84 lb    |
| ERICORE082T    | 250kV                               | 217.03 lb   |
| ERICORE024T    | 250kV                               | 66.23 lb    |
| ERICORE068T    | 250kV                               | 180.63 lb   |
| ERICORE125T    | 250kV                               | 328.83 lb   |
| ERICORE081T    | 250kV                               | 214.44 lb   |
| ERICORE069T    | 250kV                               | 183.24 lb   |
| ERICORE023T    | 250kV                               | 63.63 lb    |
| ERICORE080T    | 250kV                               | 211.84 lb   |
| ERICORE007T    | 250kV                               | 22.04 lb    |
| ERICORE070T    | 250kV                               | 185.84 lb   |
| ERICORE078T    | 250kV                               | 206.63 lb   |
| ERICORE022T    | 250kV                               | 61.03 lb    |
| ERICORE071T    | 250kV                               | 188.44 lb   |
| ERICORE122T    | 250kV                               | 321.04 lb   |

Table 5/6

| Catalog Number | Upper Termination Voltage Withstand | Unit Weight |
|----------------|-------------------------------------|-------------|
| ERICORE077T    | 250kV                               | 204.03 lb   |
| ERICORE021T    | 250kV                               | 58.44 lb    |
| ERICORE200T    | 250kV                               | 523.84 lb   |
| ERICORE072T    | 250kV                               | 191.03 lb   |
| ERICORE001T    | 250kV                               | 6.43 lb     |
| ERICORE019T    | 250kV                               | 53.23 lb    |
| ERICORE076T    | 250kV                               | 201.44 lb   |
| ERICORE075T    | 250kV                               | 198.84 lb   |
| ERICORE006T    | 250kV                               | 19.43 lb    |
| ERICORE086T    | 250kV                               | 227.44 lb   |
| ERICORE028T    | 250kV                               | 76.64 lb    |
| ERICORE026T    | 250kV                               | 71.44 lb    |
| ERICORE087T    | 250kV                               | 230.03 lb   |
| ERICORE168T    | 250kV                               | 440.63 lb   |

| Catalog Number | Upper Termination Voltage Withstand | Unit Weight |
|----------------|-------------------------------------|-------------|
| ERICORE017T    | 250kV                               | 48.03 lb    |
| ERICORE065T    | 250kV                               | 172.84 lb   |
| ERICORE060T    | 250kV                               | 159.84 lb   |
| ERICORE085T    | 250kV                               | 224.84 lb   |
| ERICORE064T    | 250kV                               | 170.24 lb   |
| ERICORE061T    | 250kV                               | 162.44 lb   |

Table 6/6


| Catalog Number | Upper Termination Voltage Withstand | Unit Weight |
|----------------|-------------------------------------|-------------|
| ERICORE066T    | 250kV                               | 175.44 lb   |
| ERICORE115T    | 250kV                               | 302.83 lb   |

## ADDITIONAL PRODUCT DETAILS

Additional lengths available in 1 m (3.28') increments.

Consult nVent ERICO technical support or the installation manual for guidance on maximum allowable lengths.

Inductance and Capacitance are per meter.



## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

#### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

#### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

#### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

#### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

**CADDY**

**ERICO**

**HOFFMAN**

**ILSCO**

**SCHROFF**

**TRACHTE**