

DPCB Punched Plain Copper Busbar, Double



FEATURES

Heavy-duty power connection

Circuit breaker, generator and prefabricated power network conductor

Alternative to large and multiple cables

Earth/ground connection

Power distribution

Rounded edges

Material: Copper



SPECIFICATIONS

Table 1/2


Catalog Number	Article Number	Width (W)	Thickness (T)	Length (L)	Hole Size (HS)	A
DPCB100X10	550380	3.94"	0.39"	68.9"	0.41"	2.95"
DPCB100X5	550440	3.94"	0.2"	68.9"	0.41"	2.95"
DPCB120X10	550390	4.72"	0.39"	68.9"	0.41"	3.74"
DPCB125X5	550450	4.92"	0.2"	68.9"	0.41"	3.94"
DPCB50X10	550350	1.97"	0.39"	68.9"	0.41"	0.98"
DPCB50X5	550410	1.97"	0.2"	68.9"	0.41"	0.98"
DPCB60X10	550360	2.36"	0.39"	68.9"	0.41"	1.38"
DPCB63X5	550420	2.48"	0.2"	68.9"	0.41"	1 1/2"
DPCB80X10	550370	3.15"	0.39"	68.9"	0.41"	2.17"
DPCB80X5	550430	3.15"	0.2"	68.9"	0.41"	2.17"

Table 2/2

Catalog Number	Article Number	B	C	Unit Weight
DPCB100X10	550380	0.98"	0.49"	31.97 lb

Catalog Number	Article Number	B	C	Unit Weight
DPCB100X5	550440	0.98"	0.49"	15.98 lb
DPCB120X10	550390	0.98"	0.49"	40.57 lb
DPCB125X5	550450	0.98"	0.49"	20.28 lb
DPCB50X10	550350	0.98"	0.49"	15 lb
DPCB50X5	550410	0.98"	0.49"	7.5 lb
DPCB60X10	550360	0.98"	0.49"	19.4 lb
DPCB63X5	550420	0.98"	0.49"	9.7 lb
DPCB80X10	550370	0.98"	0.49"	25.13 lb
DPCB80X5	550430	0.98"	0.49"	12.57 lb

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.