

PCB Plain Copper Busbar



FEATURES

Heavy-duty power connection

Circuit breaker, generator and prefabricated power network conductor

Alternative to large and multiple cables

Earth/ground connection

Power distribution

Rounded edges

Material: Copper



SPECIFICATIONS

Table 1/2


Catalog Number	Article Number	Width (W)	Thickness (T)	Length (L)	Unit Weight
PCB-2M-12X4	550790	0.47"	0.16"	78.15"	1.87 lb
PCB-1M-12X4	550780	0.47"	0.16"	38.98"	0.95 lb
PCB-2M-12X5	550770	0.47"	0.2"	78.15"	2.34 lb
PCB-4M-30X5	550620	1.18"	0.2"	157.48"	11.77 lb
PCB-2M-25X5	549600	0.98"	0.2"	78.74"	4.85 lb
PCB-4M-25X5	550610	0.98"	0.2"	157.48"	9.81 lb
PCB-4M-50X5	550640	1.97"	0.2"	157.48"	19.62 lb
PCB-4M-40X5	550630	1.57"	0.2"	157.48"	15.7 lb
PCB-4M-20X5	550600	0.79"	0.2"	157.48"	7.85 lb
PCB-2M-100X5	549640	3.94"	0.2"	78.74"	19.62 lb
PCB-4M-60X5	550650	2.36"	0.2"	157.48"	23.55 lb

Catalog Number	Article Number	Width (W)	Thickness (T)	Length (L)	Unit Weight
PCB-4M-100X5	550670	3.94"	0.2"	157.48"	39.24 lb
PCB-2M-50X5	549610	1.97"	0.2"	78.74"	9.92 lb
PCB-4M-80X5	550660	3.15"	0.2"	157.48"	31.39 lb
PCB-2M-63X5	549620	2.48"	0.2"	78.74"	12.35 lb
PCB-2M-80X5	549630	3.15"	0.2"	78.74"	15.65 lb
PCB-2M-40X10	549710	1.57"	0.39"	78.74"	15.65 lb
PCB-4M-50X10	550900	1.97"	0.39"	157.48"	39.24 lb
PCB-2M-120X10	549760	4.72"	0.39"	78.74"	47.18 lb
PCB-4M-30X10	550970	1.18"	0.39"	157.48"	23.57 lb

Table 2/2

Catalog Number	Article Number	Width (W)	Thickness (T)	Length (L)	Unit Weight
PCB-2M-80X10	549740	3.15"	0.39"	78.74"	31.31 lb
PCB-2M-30X10	549700	1.18"	0.39"	78.74"	12.13 lb
PCB-2M-60X10	549730	2.36"	0.39"	78.74"	23.59 lb
PCB-4M-40X10	550980	1.57"	0.39"	157.48"	31.42 lb
PCB-2M-100X10	549750	3.94"	0.39"	78.74"	39.24 lb
PCB-4M-160X10	550950	6.3"	0.39"	157.48"	125.66 lb
PCB-4M-60X10	550910	2.36"	0.39"	157.48"	47.07 lb
PCB-4M-120X10	550940	4.72"	0.39"	157.48"	94.36 lb
PCB-2M-50X10	549720	1.97"	0.39"	78.74"	19.62 lb
PCB-4M-80X10	550920	3.15"	0.39"	157.48"	62.83 lb
PCB-4M-100X10	550930	3.94"	0.39"	157.48"	78.48 lb

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE