

Universal Connecting Bar



nVent ERIFLEX Connecting, Earthing and Neutral Busbars are used to connect several earthing conductors within a panel and can be used in a variety of different applications including switchgear and control equipment, electrical equipment, for wind and solar power generation and in data centers. This Universal Connecting Bar can be used as a 450A current rating IEC for power distribution.

FEATURES

- Easy to wire with a hexagonal key
- Design allows for visual inspection of conductor and confirmation of connection
- For use with punched or threaded copper busbar
- High fill ratio allows output connection with or without terminal
- Quick and easy installation
- RoHS compliant



SPECIFICATIONS



Table 1/2	
Catalog Number	CB7X16
Article Number	553150
Material	Brass
Max Current Rating	450A
Number of Tunnel Connections	7
Conductor Size, IEC	(7) 1.5 - 16 mm ² Stranded

Catalog Number	CB7X16
Ferrule Conductor Size, IEC	(7) 1.5 - 16 mm ²
Conductor Size, UL	(7) #10 - #6 Solid (7) #8 - #4 Stranded
Depth (D)	0.49"
Height (H)	1.22"
Width (W)	2.68"
A	0.35"
B	0.16"
Torque (TQ)	2.58 ft·lbf
Unit Weight	0.18 lb

Table 2/2

Catalog Number	CB7X16
----------------	--------

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

