

Mounting profiles, CLPF



The mounting profiles can be fixed in all directions, providing full flexibility for the mounting of accessories, components, and other equipment.

FEATURES

Description: The CLPF profile system is a 40 mm wide and 25 mm high profile, which can be mounted in all directions on the enclosure's frame. It can also be used in combination with the CLPK and the VB profiles. By turning the profile it can be used as a standard CP20/40 profile in combination with GLM 40/6 sliding nut, to mount installation material which needs adjusting in depth. The profiles, when mounted onto the enclosure's frame are flush with the enclosure's profiles. Two rows of hole patterns for cage nut fixing and self tapping screws are provided. For 90 mm wide profiles two profiles can be mounted next to each other.

Material: Zinc plated steel.

Pack quantity: 4 profiles including snap-line for fixing.

Material: Mild Steel
Finish: Zinc Plated
Thickness: 16ga

SPECIFICATIONS

Catalog Number	Article Number	Height	Width	Depth	Compatible Enclosure Height	Compatible Enclosure Width
CLPF1000	CLPF1000	1.57in	36.4in	0.98in	47.24in min	47.24in min
CLPF1200	CLPF1200	1.57in	44.27in	0.98in	47.24in min	47.24in min
CLPF1400	CLPF1400	1.57in	52.15in	0.98in	55.12in min	55.12in min
CLPF1600	CLPF1600	1.57in	60.02in	0.98in	63in min	63in min
CLPF1800	CLPF1800	1.57in	67.89in	0.98in	70.87in min	70.87in min
CLPF2000	CLPF2000	1.57in	75.77in	0.98in	78.74in min	78.74in min
CLPF2200	CLPF2200	1.57in	83.64in	0.98in	86.61in min	86.61in min
CLPF300		1.57in	8.86in	0.98in	11.81in min	11.81in min
CLPF400	CLPF400	1.57in	12.78in	0.98in	15.75in min	15.75in min
CLPF500	CLPF500	1.57in	16.71in	0.98in	19.69in min	19.69in min
CLPF600	CLPF600	1.57in	20.65in	0.98in	23.62in min	23.62in min

Catalog Number	Article Number	Height	Width	Depth	Compatible Enclosure Height	Compatible Enclosure Width
CLPF800	CLPF800	1.57in	28.52in	0.98in	31.5in min	31.5in min

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

