


Seismic Rack Panel Kit



Used when converting a standard Free-Stand Enclosure to a Seismic Free-Stand Enclosure. Rack Panel allows rack-mount equipment to be installed in 36-inch wide enclosures. Seismic Rack Panel has EIA 310 specified square-holes (.375x.375) and larger openings to allow cables to pass through panel. Use with Seismic Panel Support Kits (included) and Seismic Mounting Plate Kits to obtain Seismic standards. Available with or without vertical cable management for copper and fiber networking cables. Kit includes one Seismic Rack Panel and two Seismic Panel Supports with hardware.

FEATURES

Used when converting a standard Free-Stand Enclosure to a Seismic Free-Stand Enclosure

Rack Panel allows rack-mount equipment to be installed in 36-inch wide enclosures

Seismic Rack Panel has EIA 310 specified square-holes (.375x.375) and larger openings to allow cables to pass through panel

Use with Seismic Panel Support Kits (included) and Seismic Mounting Plate Kits to obtain Seismic standards

Available with or without vertical cable management for copper and fiber networking cables

Kit includes one Seismic Rack Panel and two Seismic Panel Supports with hardware

SPECIFICATIONS

Catalog Number	Article Number	Material	Finish	Color	Color Code	Thickness
A72P36RP	35457	Mild Steel	Powder Coated	Light Gray	RAL 7035	12ga
A72P36RPC	35453	Mild Steel	Powder Coated	Light Gray	RAL 7035	12ga
A90P36RP	35461	Mild Steel	Powder Coated	Light Gray	RAL 7035	12ga
A90P36RPC	35455	Mild Steel	Powder Coated	Light Gray	RAL 7035	12ga

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.