

Window Door, ADC



Electrical components can be viewed while the door is closed, which keeps unauthorized personnel out and maintains the ingress protection.

FEATURES

Description: To replace the standard door, it provides a clear view of the components installed inside the enclosure. The lock(s) are interchangeable with all nVent HOFFMAN's standard lock(s).

Material: 1.2 mm mild steel / 1.5 mm for enclosures with a height or width of 500 mm or greater / 2 mm for enclosures with a height or width of 800 mm or greater and 4 mm clear safety glass.

Finish: RAL 7035 structured powder coating.

Protection: Complies with IP 55, TYPE 12, 13, IK 07.

Pack quantity: 1 door.

Material: Mild Steel
Finish: Powder Coated
Color: Light Gray
Color Code: RAL 7035

SPECIFICATIONS

Catalog Number	Article Number	Height	Width	Depth	Thickness	Latch Quantity
ADC03025R5	ADC03025R5	11.61in	9.65in	0.61in	18ga	1
ADC03030R5	ADC03030R5	11.61in	11.61in	0.61in	18ga	1
ADC04030R5	ADC04030R5	15.55in	11.61in	0.61in	18ga	1
ADC04040R5	ADC04040R5	15.55in	15.55in	0.61in	18ga	1
ADC05030R5	ADC05030R5	19.49in	11.61in	0.61in	16ga	1
ADC05040R5	ADC05040R5	19.49in	15.55in	0.61in	16ga	1
ADC06040R5	ADC06040R5	23.43in	15.55in	0.61in	16ga	2
ADC06050R5	ADC06050R5	23.43in	19.49in	0.61in	16ga	2
ADC06060R5	ADC06060R5	23.43in	23.43in	0.61in	16ga	2
ADC07050R5	ADC07050R5	27.36in	19.49in	0.61in	16ga	2
ADC08060R5	ADC08060R5	31.3in	23.43in	0.61in	14ga	2
ADC10060R5	ADC10060R5	39.17in	23.43in	0.61in	14ga	1

Catalog Number	Article Number	Height	Width	Depth	Thickness	Latch Quantity
ADC10080R5	ADC10080R5	39.17in	31.3in	0.61in	14ga	1
ADC12060R5	ADC12060R5	47.05in	23.43in	0.61in	14ga	1
ADC12080R5	ADC12080R5	47.05in	31.3in	0.61in	14ga	1

ADDITIONAL PRODUCT DETAILS

* 3 point espagnolette locking. Not suitable for AFS.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

