

ZonEx Non-Metallic Terminal Enclosure

ZonEx Non-Metallic Terminal Enclosure is ideal for field terminations in hazardous locations. The enclosure meets national and international standards and certifications. It can be used to protect equipment and terminations from corrosive contaminants while meeting rigorous demands. The cabinet is ideal for either panel- or din-mounted components. The enclosures meet ATEX Directives 2014/35/EU and IECEx standards for increased safety in housing electrical components in Zone 1 and Zone 2 applications.

INDUSTRY STANDARDS

Type 4, 4X, 12; File No. E61997

UL508A Listed

cUL Listed per CSA C22.2 No. 94; Type 4, 4X, 12; File No. E61997

ATEX Directive 2014/34/EU

ATEX

IBExU16ATEX1234U

Ex eb IIC Gb

Ex ta IIIC Da IP66

EN60079-0

EN60079-7

EN60079-31

Service temperature -55C to +135C

IECEx

IECEx IBE16.0049U

Ex eb IIC Gb

Ex ta IIIC Da IP66

IEC 60079-0

IEC 60079-7

IEC 60079-31

Service temperature -55C to +135C

NEMA / EEMAC Type 4, 4X, 12

IEC 60529, IP66



FEATURES

Compression-molded, high-impact strength, polyester body and cover

Cover includes recessed, retained, combination head (Straight blade, Phillips and Torx drive) M4 or M6 stainless steel Type 316 screws

Retained, continuous, high-temperature silicon gasket within a labyrinth seal between cover and body

Durable and reusable, internal M4 or M6 stainless steel inserts for DIN- and Panel-mounting

Covered mounting screw provisions outside of gasketed area, sized M4 (#8) or M6 (1/4-in.)

Mounting location dimensions are molded into the back side of the enclosure

Panel mounting screws included, M4 or M6

Compression-molded fiberglass with added agents to address static charge build-up

High-impact strength as well as high temperature-rated

Increased Safety: Ex e applications

Optional panels are pre-plated steel, 1.5mm (16 ga.) thick; or 2mm composite

Material: Fiberglass
Finish: Smooth Gloss
Color: Black

SPECIFICATIONS

Catalog Number	Article Number	Height	Width	Depth	Thickness	Mounting Screw Size
EXE1107555	26235	4.33in	2.95in	2.17in	0.16in	#8
EXE1107575	26236	4.33in	2.95in	2.95in	0.16in	#8
EXE12212090	26243	4.8in	4.72in	3.54in	0.16in	1/4"
EXE16016090	26245	6.3in	6.3in	3.54in	0.16in	1/4"
EXE1607555	26237	6.3in	2.95in	2.17in	0.16in	#8
EXE1607575	26238	6.3in	2.95in	2.95in	0.16in	#8
EXE1907555	26241	7.48in	2.95in	2.17in	0.16in	#8
EXE1907575	26242	7.48in	2.95in	2.95in	0.16in	#8
EXE22012090	26244	8.66in	4.72in	3.54in	0.16in	1/4"
EXE255250120	26251	10.04in	9.84in	4.72in	0.16in	1/4"
EXE26016090	26246	10.24in	6.3in	3.54in	0.16in	1/4"
EXE36016090	26247	14.17in	6.3in	3.54in	0.16in	1/4"
EXE400250120	26252	15.75in	9.84in	4.72in	0.16in	1/4"
EXE400405120	26253	15.75in	15.94in	4.72in	0.16in	1/4"
EXE56016090	26248	22.05in	6.3in	3.54in	0.16in	1/4"
EXE807555	26233	3.15in	2.95in	2.17in	0.16in	#8
EXE807575	26234	3.15in	2.95in	2.95in	0.16in	#8

ADDITIONAL PRODUCT DETAILS

Intrinsically safe terminal blocks can be installed through modification program to provide a populated enclosure. IECEx populated enclosures require IECEx certified components specifically listed in the approving Certification (see IECEx SIR 09.0100 for more detail).

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

⚠ WARNING: This product can expose you to chemicals including styrene, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov.



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.