


# Cooling Circuitry STD 3U 76TE mont. W/ QD

New

## CATALOG NUMBER

**20740-050**



The Easy Swap LFT Cooling Circuit is a "back-pack" cooling Unit for a 3U subrack rear area. With its width of 76 HP it allows an additional 8 HP front panel to be mounted aside for the mains power inlet to the subrack. Up to 3 Easy Swap Cold plates can be attached to the unit either by the Easy Swap LFT Direct Connection Set or the Quick Disconnect Set. It dissipates the heat of the Cold Plates with a heat exchanger and 2 low noise fans to the back.

## FEATURES

Cooling Circuitry for up to 3 Easy Swap LFT Cold Plates

3 U height, 76 HP width. Can be mounted at the backside of a 3U subrack

Up to 600 W of cooling capacity at 50°C environmental temperature

Accepts demineralized water or Water Glycol mix (25% Glycol recommended)

Low noise fans and pump

Easy Swap LFT Cold Plates can be connected to Cooling Circuitry either with Direct Connection Set or Quick Disconnect Set



## PRODUCT ATTRIBUTES

Package Quantity: 1

Product Family: Liquid Board Cooling

Product Type: Conductor Block

Type: Liquid Cooling Circuitry

Width: 383.8mm

Works With: Subracks

\*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched

from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address, parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

ADDITIONAL PRODUCT DETAILS

Please order the Cold Plates and Connection sets separately

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

