

nVent CADDY Truss-T Bar Joist Hanger, Bottom Chord, 3/8" Rod

CATALOG NUMBER

CTH037BC



FEATURES

Easily installs on the bottom chord of engineered open web bar joists from underneath, limiting overhead work

Innovative attachment effortlessly slides through the middle slot of open web bar joists and quickly locks into place when put under load

Installation of the complete, self-contained system can be accomplished with one hand and requires no additional special tools

The unique design of the nVent CADDY Truss-T hanger does not need to be tightened like a traditional beam clamp, providing greater adjustability and speed during system alignment

Prefabricated single pipe hanger and multi-pipe/tube trapeze assemblies can be prefabricated on the ground or in the shop, and easily hung by the installer

Concentrically loading the bar joist chord eliminates torsion and/or distortion, adhering to the strict rules established by the Steel Joist Institute (SJI)

The increased load carrying capacity results in the product being UL listed to support a maximum of 8" Schedule 40 pipe


Included square washer with integrated threaded nut eliminates the need for loose hardware



PRODUCT ATTRIBUTES

Material: Steel
Finish: Pregalvanized
Static Load Safety Factor: 3.5:1
Rod Size (RS): 3/8"
A: 3"
B: 1 1/4"
C: 4 1/2"
D: 1/2" - 1"
Static Load (F): 1200lbf

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

