

Speed Link SLC with Hammer-On Flange Clip 2 mm Wire x 32.8', 5/16"–1/2" Flange

CATALOG NUMBER

SLC2L104H58



The nVent CADDY Speed Link SLC with Hammer-On Flange Clip delivers a fast, dependable way to suspend duct from most beams, helping crews move quickly and reduce time on elevated surfaces. Offered in three cable lengths to cover a wide range of applications, the Speed Link SLC with Hammer-On Flange helps reduce on-site measuring and rework by giving installers a ready-to-use solution. The tool-free locking device design makes adjustment simple and flexible when working with unknown structures or changing field conditions. Leveling and final positioning can be done quickly without specialized tools, ensuring contractors spend less time installing and more time finishing the job.

FEATURES

Includes wire and is assembled to a hammer-on flange clip end fitting

Quickly and easily attaches to beams

Installs with just a hammer

Compatible with nVent CADDY Speed Link SLS Locking Device and nVent CADDY SLK Locking Device in 2mm and 3mm sizes (sold separately)

PRODUCT ATTRIBUTES

Material: Steel;Spring Steel

Finish: nVent CADDY Armour

Static Load Safety Factor: 5:1

Complies With: SMACNA HVAC-DCS


Wire Rope Diameter: 2 mm

Wire Rope Length: 32.8'

Flange Thickness (FT): 5/16" - 1/2"

Static Load (F): 100lbf

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

