

nVent CADDY Self-Cutting Cable Tie



The nVent CADDY Self-Cutting Cable Tie is a versatile, tool-free datacom solution for bundling large amounts of cables. This simple, yet innovative product features a built-in cutting blade to ensure a secure fastening and a safe, clean tie-off finish. Made from durable 6/6 nylon, the Self-Cutting Cable Tie boasts a robust 50lb/ 22Kg of tensile strength.

FEATURES

- Eliminates sharp edges and protects exposed skin from cuts during installation
- Lock and twist to cut, no cutting tools required
- Different colors including a black UV-protected version to meet specific needs
- RoHS (Restriction of Hazardous Substances Directive) compliant
- Halogen free
- cULus Listed to UL 62275/CSA C22.2 No. 62275, UL Certified to IEC 62275

Complies With: IEC® 60695-2-11 (Glow Wire Test 960 °C)





SPECIFICATIONS

Catalog Number	Material	Color	Length (L)	Width (W)	Installation Temperature	Operating Temperature
CADTIESC11CBAP	Nylon, Stainless Steel 301 (EN 1.4310)	Black	11"	0.17"	0 °F Min	-4 to 185 °F
CADTIESC11CNAP	Nylon, Stainless Steel 301 (EN 1.4310)	Natural	11"	0.17"	0 °F Min	-4 to 185 °F
CADTIESC14CBAP	Nylon, Stainless Steel 301 (EN 1.4310)	Black	14"	0.17"	0 °F Min	-4 to 185 °F
CADTIESC14CNAP	Nylon, Stainless Steel 301 (EN 1.4310)	Natural	14"	0.17"	0 °F Min	-4 to 185 °F
CADTIESC8CBAP	Nylon, Stainless Steel 301 (EN 1.4310)	Black	8"	0.17"	0 °F Min	-4 to 185 °F

Catalog Number	Material	Color	Length (L)	Width (W)	Installation Temperature	Operating Temperature
CADTIESC8CNAP	Nylon, Stainless Steel 301 (EN 1.4310)	Natural	8"	0.17"	0 °F Min	-4 to 185 °F
CADTIESC11CRDP	Nylon, Stainless Steel 301 (EN 1.4310)	Burgundy	11"	0.17"	0 °F Min	-4 to 185 °F
CADTIESC11MBAP	Nylon, Stainless Steel 301 (EN 1.4310)	Black	11"	0.17"	0 °F Min	-4 to 185 °F
CADTIESC11MNAP	Nylon, Stainless Steel 301 (EN 1.4310)	Natural	11"	0.17"	0 °F Min	-4 to 185 °F
CADTIESC11MRDP	Nylon, Stainless Steel 301 (EN 1.4310)	Burgundy	11"	0.17"	0 °F Min	-4 to 185 °F
CADTIESC14CRDP	Nylon, Stainless Steel 301 (EN 1.4310)	Burgundy	14"	0.17"	0 °F Min	-4 to 185 °F
CADTIESC14MBAP	Nylon, Stainless Steel 301 (EN 1.4310)	Black	14"	0.17"	0 °F Min	-4 to 185 °F
CADTIESC14MNAP	Nylon, Stainless Steel 301 (EN 1.4310)	Natural	14"	0.17"	0 °F Min	-4 to 185 °F
CADTIESC14MRDP	Nylon, Stainless Steel 301 (EN 1.4310)	Burgundy	14"	0.17"	0 °F Min	-4 to 185 °F
CADTIESC8CRDP	Nylon, Stainless Steel 301 (EN 1.4310)	Burgundy	8"	0.17"	0 °F Min	-4 to 185 °F
CADTIESC8MBAP	Nylon, Stainless Steel 301 (EN 1.4310)	Black	8"	0.17"	0 °F Min	-4 to 185 °F
CADTIESC8MNAP	Nylon, Stainless Steel 301 (EN 1.4310)	Natural	8"	0.17"	0 °F Min	-4 to 185 °F
CADTIESC8MRDP	Nylon, Stainless Steel 301 (EN 1.4310)	Burgundy	8"	0.17"	0 °F Min	-4 to 185 °F

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

