

Wire Basket Tray, Shaped Wire

The construction of the nVent CADDY Wire Basket Tray, Shaped Wire eliminates stress and pressure points on today's high-speed/performance cabling media. The backbone of the platform features our "Shaped Tray" technology—offering substantial support improvement over traditional wire mesh tray. This technology increases support by 400% while reducing cable strain up to 65%, protecting high-performance and fiber optic cable for the life of the installation.

FEATURES

Provides optimal support for high-performance data cable, up to and including fiber optic, Cat 5e, Cat 6, Cat 6A, and Cat 7

UL Classified as an equipment ground conductor, no field removal of paint required

T-Weld edge wire for cable and installer protection

Mill Certificates are available to document recycled content for possible LEED credits/certification

Material: Steel

SPECIFICATIONS

Table 1/5

Catalog Number	Finish	Color	Height (H)	Width (W)	Length (L)	Unit Weight	Certifications
WBT2X8SPW	Pregalvanized, Powder Coated	Pewter	2	8	118"	9.78 lb	UL, cUL
WBT2X6SPW	Pregalvanized, Powder Coated	Pewter	2	6	118"	9 lb	cUL, UL
WBT2X12SPW	Pregalvanized, Powder Coated	Pewter	2	12	118"	14 lb	cUL, UL
WBT2X24SPW	Pregalvanized, Powder Coated	Pewter	2	24	118"	24 lb	UL, cUL
WBT2X6SWH	Pregalvanized, Powder Coated	White	2	6	118"	9 lb	UL, cUL

Catalog Number	Finish	Color	Height(H)	Width(W)	Length(L)	UnitWeight	Certifications
WBT2X24SBA	Pregalvanized, Powder Coated	Black	2	24	118"	24 lb	cUL, UL
WBT2X8S	Pregalvanized		2	8	118"	10 lb	UL
WBT2X12SWH	Pregalvanized, Powder Coated	White	2	12	118"	14 lb	cUL, UL
WBT2X8SBA	Pregalvanized, Powder Coated	Black	2	8	118"	9.78 lb	UL, cUL
WBT2X20SWH	Pregalvanized, Powder Coated	White	2	20	118"	21.59 lb	UL, cUL
WBT2X16S	Pregalvanized		2	16	118"	18 lb	UL
WBT2X24S	Pregalvanized		2	24	118"	24 lb	UL
WBT2X20SBA	Pregalvanized, Powder Coated	Black	2	20	118"	21.59 lb	UL, cUL
WBT2X8SWH	Pregalvanized, Powder Coated	White	2	8	118"	9.78 lb	UL, cUL
WBT2X16SBA	Pregalvanized, Powder Coated	Black	2	16	118"	18 lb	UL, cUL
WBT2X20S	Pregalvanized		2	20	118"	22 lb	UL
WBT2X18SWH	Pregalvanized, Powder Coated	White	2	18	118"	19 lb	UL, cUL
WBT2X18SPW	Pregalvanized, Powder Coated	Pewter	2	18	118"	19 lb	UL, cUL
WBT2X16SWH	Pregalvanized, Powder Coated	White	2	16	118"	18 lb	UL, cUL
WBT2X18SBA	Pregalvanized, Powder Coated	Black	2	18	118"	19 lb	UL, cUL

Table 2/5

Catalog Number	Finish	Color	Height (H)	Width (W)	Length (L)	Unit Weight	Certifications
WBT2X18S	Pregalvanized		2	18	118"	19 lb	UL
WBT2X12SBA	Pregalvanized, Powder Coated	Black	2	12	118"	14 lb	cUL, UL
WBT2X4SBA	Pregalvanized, Powder Coated	Black	2	4	118"	8 lb	cUL, UL
WBT2X4SWH	Pregalvanized, Powder Coated	White	2	4	118"	8 lb	cUL, UL
WBT2X6S	Pregalvanized		2	6	118"	9 lb	UL
WBT2X4S	Pregalvanized		2	4	118"	8 lb	UL

Catalog Number	Finish	Color	Height(H)	Width(W)	Length(L)	UnitWeight	Certifications
WBT2X4SPW	Pregalvanized, Powder Coated	Pewter	2	4	118"	8 lb	cUL, UL
WBT2X12S	Pregalvanized		2	12	118"	14 lb	UL
WBT2X6SBA	Pregalvanized, Powder Coated	Black	2	6	118"	9 lb	UL, cUL
WBT2X24SWH	Pregalvanized, Powder Coated	White	2	24	118"	24 lb	UL, cUL
WBT6X20SBA	Pregalvanized, Powder Coated	Black	6	20	118"	29 lb	UL, cUL
WBT6X20S	Pregalvanized		6	20	118"	29 lb	UL
WBT4X8S	Pregalvanized		4	8	118"	14 lb	UL
WBT4X6S	Pregalvanized		4	6	118"	11 lb	UL
WBT6X16SBA	Pregalvanized, Powder Coated	Black	6	16	118"	24 lb	UL, cUL
WBT4X12S	Pregalvanized		4	12	118"	18 lb	UL
WBT4X6SWH	Pregalvanized, Powder Coated	White	4	6	118"	11 lb	UL, cUL
WBT6X24S	Pregalvanized		6	24	118"	32.01 lb	UL
WBT4X12SBA	Pregalvanized, Powder Coated	Black	4	12	118"	18 lb	UL, cUL
WBT6X18SWH	Pregalvanized, Powder Coated	White	6	18	118"	25 lb	cUL, UL

Table 3/5

Catalog Number	Finish	Color	Height (H)	Width (W)	Length (L)	Unit Weight	Certifications
WBT4X12SPW	Pregalvanized, Powder Coated	Pewter	4	12	118"	18 lb	UL, cUL
WBT6X16S	Pregalvanized		6	16	118"	24 lb	UL
WBT6X20SPW	Pregalvanized, Powder Coated	Pewter	6	20	118"	29 lb	UL, cUL
WBT4X6SPW	Pregalvanized, Powder Coated	Pewter	4	6	118"	11 lb	UL, cUL
WBT4X12SWH	Pregalvanized, Powder Coated	White	4	12	118"	18 lb	UL, cUL
WBT4X6SBA	Pregalvanized, Powder Coated	Black	4	6	118"	11 lb	UL, cUL
WBT4X16S	Pregalvanized		4	16	118"	22 lb	UL

Catalog Number	Finish	Color	Height(H)	Width(W)	Length(L)	UnitWeight	Certifications
WBT4X8SWH	Pregalvanized, Powder Coated	White	4	8	118"	14 lb	cUL, UL
WBT6X16SWH	Pregalvanized, Powder Coated	White	6	16	118"	24 lb	cUL, UL
WBT6X12SBA	Pregalvanized, Powder Coated	Black	6	12	118"	22 lb	UL, cUL
WBT6X12SPW	Pregalvanized, Powder Coated	Pewter	6	12	118"	22 lb	cUL, UL
WBT6X18S	Pregalvanized		6	18	118"	25 lb	UL
WBT6X12S	Pregalvanized		6	12	118"	22 lb	UL
WBT6X16SPW	Pregalvanized, Powder Coated	Pewter	6	16	118"	24 lb	cUL, UL
WBT6X18SBA	Pregalvanized, Powder Coated	Black	6	18	118"	25 lb	cUL, UL
WBT4X24S	Pregalvanized		4	24	118"	29 lb	UL
WBT6X18SPW	Pregalvanized, Powder Coated	Pewter	6	18	118"	25 lb	cUL, UL
WBT4X8SPW	Pregalvanized, Powder Coated	Pewter	4	8	118"	14 lb	UL, cUL
WBT6X12SWH	Pregalvanized, Powder Coated	White	6	12	118"	22 lb	cUL, UL
WBT4X8SBA	Pregalvanized, Powder Coated	Black	4	8	118"	14 lb	UL, cUL

Table 4/5

Catalog Number	Finish	Color	Height (H)	Width (W)	Length (L)	Unit Weight	Certifications
WBT4X20S	Pregalvanized		4	20	118"	24 lb	UL
WBT6X24SPW	Pregalvanized, Powder Coated	Pewter	6	24	118"	32.01 lb	UL
WBT4X24SBA	Pregalvanized, Powder Coated	Black	4	24	118"	29 lb	cUL, UL
WBT4X20SPW	Pregalvanized, Powder Coated	Pewter	4	20	118"	24 lb	UL, cUL
WBT4X16SWH	Pregalvanized, Powder Coated	White	4	16	118"	22 lb	cUL, UL
WBT4X24SPW	Pregalvanized, Powder Coated	Pewter	4	24	118"	29 lb	UL, cUL
WBT6X8SPW	Pregalvanized, Powder Coated	Pewter	6	8	118"	18 lb	UL, cUL

Catalog Number	Finish	Color	Height(H)	Width(W)	Length(L)	UnitWeight	Certifications
WBT4X20SBA	Pregalvanized, Powder Coated	Black	4	20	118"	24 lb	UL, cUL
WBT4X18S	Pregalvanized		4	18	118"	23 lb	UL
WBT6X24SWH	Pregalvanized, Powder Coated	White	6	24	118"	32.01 lb	UL, cUL
WBT4X4SPW	Pregalvanized, Powder Coated	Pewter	4	4	118"	10 lb	cUL, UL
WBT4X24SWH	Pregalvanized, Powder Coated	White	4	24	118"	29 lb	cUL, UL
WBT6X8SBA	Pregalvanized, Powder Coated	Black	6	8	118"	18 lb	UL, cUL
WBT4X4SBA	Pregalvanized, Powder Coated	Black	4	4	118"	10 lb	cUL, UL
WBT4X18SBA	Pregalvanized, Powder Coated	Black	4	18	118"	23 lb	UL, cUL
WBT4X18SWH	Pregalvanized, Powder Coated	White	4	18	118"	23 lb	UL, cUL
WBT4X4S	Pregalvanized		4	4	118"	10 lb	UL
WBT4X18SPW	Pregalvanized, Powder Coated	Pewter	4	18	118"	23 lb	UL, cUL
WBT6X8S	Pregalvanized		6	8	118"	18 lb	UL
WBT6X24SBA	Pregalvanized, Powder Coated	Black	6	24	118"	32.01 lb	cUL, UL

Table 5/5

Catalog Number	Finish	Color	Height (H)	Width (W)	Length (L)	Unit Weight	Certifications
WBT6X8SWH	Pregalvanized, Powder Coated	White	6	8	118"	18 lb	UL, cUL
WBT4X4SWH	Pregalvanized, Powder Coated	White	4	4	118"	10 lb	UL, cUL
WBT4X20SWH	Pregalvanized, Powder Coated	White	4	20	118"	24 lb	UL, cUL
WBT4X16SPW	Pregalvanized, Powder Coated	Pewter	4	16	118"	22 lb	cUL, UL
WBT4X16SBA	Pregalvanized, Powder Coated	Black	4	16	118"	22 lb	cUL, UL

2" DEEP TRAY	
Tray Size	Splice Qty
2X4	2
2X6	3
2X8	3
2X12	3
2X16	4
2X18	4
2X20	4
2X22	5
2X24	5
2X26	6
2X28	6
2X30	6
2X32	7
2X34	7
2X36	8
2X38	8
2X40	9
These products are also available for Shaped Cable Tray and can be found by including an S to the end of any part number above	

4" DEEP TRAY	
Tray Size	Splice Qty
4X4	3
4X6	3
4X8	3
4X12	3
4X16	4
4X18	4
4X20	4
4X22	4
4X24	5
4X28	5
4X30	6
4X32	6
4X34	6
4X36	7
These products are also available for Shaped Cable Tray and can be found by including an S to the end of any part number above	

6" DEEP TRAY	
Tray Size	Splice Qty
6X8	3
6X12	3
6X16	3
6X18	4
6X20	4
6X22	4
6X24	4
6X26	5
6X28	5
6X30	5
6X32	6
6X34	6
6X36	7
These products are also available for Shaped Cable Tray and can be found by including an S to the end of any part number above	

DIAGRAMS

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE

