

Threaded Coupler for Copper-Bonded Ground Rod, Threaded

FEATURES


High-strength couplings are threaded and chamfered at both ends for easy driving

Corrosion-resistant couplings ensure permanent, low resistance copper-to-copper connections



SPECIFICATIONS

Catalog Number	Material	Ground Rod Diameter, Nominal	Length (L)	Thread Size (TS)	Unit Weight	Complies With	Certifications
CR12S	Bronze	9/16"	2 1/2"	9/16" UNC	0.16 lb	EN IEC 62561-2	UL, cUL, CSA, CSA-US
CR58	Bronze	5/8"	2.4"	5/8" UNC	0.19 lb	EN IEC 62561-2	UL, cUL, RUS, CSA-US, CSA
CR34	Bronze	3/4"	3"	3/4" UNC	0.34 lb		RUS, CSA-US, UL, cUL, CSA
CR100	Silicon Bronze	1"	3.9"	1" UNC	0.78 lb	EN IEC 62561-2	cUL, UL



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

⚠ WARNING: This product can expose you to chemicals including lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE